

11 Utility/Bar Sink, DURASTONE®






Form, function and fashion...the Model 11 Utility/Hobby/Bar Sink delivers all that and more in a premium quality fiberglass sink that will look great wherever it's installed.

Design Features:

- Molded using matched metal molds with premium DURASTONE® fiberglass blended with special resins for extra strength and durability
- Extra deep, 9½" self-rimming 7-gallon capacity bowl
- Reinforced 3½" drain opening for standard basket drain (not included)
- Connects to standard 1½" P-Trap
- 17"x 20" Size makes it ideal for narrow or cramped countertops
- Accommodates single or dual-handle faucet with 4" or 8" center
- Available in white, bone and biscuit
- Stain resistant, semi-gloss, colorfast finish; easy to clean

Code Approved:

- American National Standards Institute (ANSI) – Specification Z124.6 
- International Association of Plumbing and Mechanical Officials (IAPMO®) – Listed file #0820 
- Warnock Hersey (Canada) – CSA #B45.0 and B45.5 

Specifications

Dimensions	Length	Width	Depth	Model	Color
Overall	20"	17"	10"	11	White
Inside Bowl	15"	14"	19½"	11BN	Bone
Cutout	18½"	15½"	—	11BT	Biscuit

General: Furnish and install as shown on plans, a Countertop Sink Model 11 as manufactured by E.L. Mustee & Sons, Inc. Material composition shall be molded fiberglass, using matched metal molds under extreme heat and pressure. One-piece seamless construction with self-rimming edge. 3½" drain opening. Overall size: 20" x 17" x 10". Shall meet ANSI Specification Z 124.6. Color: _____ (White, Bone, Biscuit).

