

# PIG® DrainBlocker® Drain Cover with DuPont Elvaloy®

#PLR405 - For Square Drains up to 42"



Protect your drains with the patented design that seals tight and won't rip. Guaranteed.

- Patented two-layer design seals tight to protect drains and won't rip. Guaranteed.
- Use cover for quick spill response or long-term, outdoor deployment without worrying about degradation
- Vinyl composite top layer resists stretching, ripping and tearing
- DuPont Elvaloy technology provides lifelong flexibility plus chemical, UV and infrared light resistance to vinyl top
- Super-sealing urethane bottom layer conforms to uneven surfaces and tightly seals drain openings to block liquid
- Cover withstands prolonged exposure to diesel fuel and gasoline, even when completely submerged
- Ideal for drain protection where liquid transfers, washdowns or other leak- and spill-prone jobs are common
- Eliminates the need to frequently deploy and remove a temporary cover or permanently seal your drains
- High-visibility yellow top layer draws attention to spills for increased safety
- Need a custom size? Call 1-800-HOT-HOGS (468-4647)
- Note: Elvaloy top can become slippery when wet. Please use caution.



**New Pig**

By Phone:  
**1-855-493-HOGS**

Online:  
**newpig.com**

Email:  
**hothogs@newpig.com**

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.  
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: PLR405 - Pg 1 of 2

## PLR405 Specifications

<b>Style:</b>	Walk-on
<b>Use With:</b>	Square Drains up to 42"
<b>Color:</b>	Top - Yellow, Bottom - Black
<b>Dimensions:</b>	48" W x 48" L x 0.3125" H
<b>Intended For:</b>	Smooth Surface
<b>Max liquid temp exposure:</b>	225°F for up to 30 minutes
<b>Storage Temp Range:</b>	0° — 120°F
<b>Temperature Limit:</b>	0° — 160°F up to 12 months
<b>UV Resistant:</b>	Yes
<b>Sold as:</b>	1 each
<b>Weight:</b>	36 lbs.
<b>New Pig Patent:</b>	8,117,686
<b># per Pallet:</b>	25
<b>Composition:</b>	Urethane; DuPont™ Elvaloy® Vinyl
<b>UNSPSC:</b>	40141739

## PLR405 Metric Equivalent

<b>Dimensions:</b>	121.9cm W x 121.9cm L x 7.9mm H
<b>Weight:</b>	16.3 kg

## Technical Information

### Warnings & Restrictions:

#### Urethane Notice

Due to the nature of softer urethane, the physical properties of these products may change over time with exposure to certain environmental conditions like temperature, humidity, and UV radiation. Typical life expectancy is 5 years. Please inspect the stored product regularly to ensure it is in a usable state. For more details and for chemical compatibility, please call Technical Services.

### Regulations and Compliance:

40 CFR 122.26 - When applying for a National Pollutant Discharge Elimination System (NPDES) permit, facilities must have a plan in place that describes actions, procedures, control techniques, management practices and equipment available to prevent illegal discharge of pollutants into waterways.

40 CFR 112.7 - SPCC planning requirements state that facilities subject to these regulations must have written plans in place discussing the products, countermeasures and procedures that are in place, or will be taken by the facility to prevent discharge of oil into waters of the United States.

### Technical Documents:

(Available at [newpig.com](http://newpig.com))

Product Data Sheet (PDS)

Safety Data Sheet (SDS)

Chemical Compatibility (CCG)



**New Pig**

By Phone:  
**1-855-493-HOGS**

Online:  
**newpig.com**

Email:  
**hothogs@newpig.com**

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.  
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: PLR405 - Pg 2 of 2