

PIG® Pipe Leak Diverter Bucket Kit

#TLS669 - 18" x 18"



Quickly respond to pipe leaks with a kit that's loaded with supplies to divert leaks AND repair the pipe.

- Contains essential supplies for rapid response to a pipe leak, all in a compact, 6.5-gallon pail
- Nonpermeable tarp is vinyl-coated for strength and durability; resists punctures, UV and mildew
- Straps are included for fast setup and response
- Preinstalled quick connect set lets you attach hose to leak diverter in seconds without screwing or twisting
- Flow rate of 3.33 gallons per minute when used with a 1/2" ID hose
- Pail with printed "Caution" message can be used as a collection container for diverted liquid
- High-visibility yellow PIG® Mat pads soak up puddles to keep floors dry and safe; printed "Caution" message draws attention to spill
- PIG® All-Purpose Wipers are great for wiping down diverter kit before storage or for cleaning up small spills
- PIG® Pipe Wrap and PIG® Multi-Purpose Repair Putty permanently patch pressurized pipes up to 2" in diameter
- Need a custom size or solution? Just call 1-800-HOT-HOGS (468-4647)



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS669 - Pg 1 of 3

TLS669 Specifications

Use With:	Pipes
Drainage Hose Included:	Yes
Flow Rate:	3.33 gal. per Minute
Grommets/D-Rings:	4 Grommets
Hanging Straps Included:	Yes
Hose Connector:	.75" w/ Quick Connect
Installation Method:	Hanging Straps
Thickness:	16 mil
Sold as:	1 each
# per Pallet:	32
Composition:	Leak Diverter - 67% PVC, 33% Polyester Hose - PVC Straps - Rubber Bucket - Plastic Mats - Polypropylene
Includes:	1 - 18" Ext. Dia. x 18" H Pipe Leak Diverter 1 - 25' L Drainage Hose 4 - 14" L Hanging Straps 1 - 6.5 gal. Bucket 1 - 30 Pack "CAUTION" PIG® Mat Pads 2 - 25 Pack PIG® All-Purpose Wipers 1 - Pack PIG® Pipe Wrap for 2.5" to 4" Dia. Pipes 1 - Tube PIG® Multi-Purpose Repair Putty
UNSPSC:	24141506

Technical Information

Warnings & Restrictions:

Chemical Resistance
Limited chemical-resistance; not suitable for temperatures over 190° F/88° C.
This product is subject to export restrictions and cannot be shipped to: Canada, European Union, Japan.

Technical Documents:

(Available at newpig.com)
Product Data Sheet (PDS)
Safety Data Sheet (SDS)
Chemical Compatibility (CCG)



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304
© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS669 - Pg 3 of 3