

# PIG® Roof Leak Diverter Bucket Kit with Absorbents

#TLS667 - 5' x 5'



Our portable Leak Diverter Bucket Kits are perfect for grab-and-go response to overhead leaks.

- Contains supplies for rapid response to roof leaks, all in a 6.5-gallon pail
- Pail can be used as a collection container for diverted liquid; printed "Caution" message doubles as a warning sign
- Nonpermeable tarp is vinyl coated for strength and durability; resists punctures, UV and mildew for long life
- Hangs easily in problem spots to catch nuisance leaks and channel them to a floor drain or collection container
- Flow rate of 3.33 gallons per minute when used with a 1/2" ID hose
- Translucent material lets light through and allows easy monitoring of leak
- Preinstalled quick connect set lets you attach hose to leak diverter in seconds
- Adjustable straps allow fast setup and response
- High-visibility yellow PIG Mat Pads soak up puddles to keep floors safe; "Caution" message draws attention to spill
- PIG All-Purpose Wipers are great for wiping down diverter kit before storage or for cleaning up small spills
- Need a custom size or solution? Just call 1-800-HOT-HOGS (468-4647)



New Pig

By Phone:  
1-855-493-HOGS

Online:  
newpig.com

Email:  
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.  
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS667 - Pg 1 of 3

# TLS667 Specifications

<b>Use With:</b>	Roofs
<b>Drainage Hose Included:</b>	Yes
<b>Flow Rate:</b>	3.33 gal. per Minute
<b>Grommets/D-Rings:</b>	4 Grommets
<b>Hanging Straps Included:</b>	Yes
<b>Hose Connector:</b>	.75" w/ Quick Connect
<b>Installation Method:</b>	Hanging Straps
<b>Thickness:</b>	16 mil
<b>Sold as:</b>	1 each
<b># per Pallet:</b>	32
<b>Composition:</b>	Leak Diverter - 67% PVC, 33% Polyester Hose - PVC Straps - Nylon Bucket - Plastic Mats - Polypropylene
<b>Includes:</b>	1 - 5' L x 5' W Leak Diverter 1 - 25' L Drainage Hose 4 - 60" L Adjustable Hanging Straps 1 - 6.5 gal. Bucket 1 - 30 Pack "CAUTION" PIG® Mat Pads 2 - 25 Pack PIG® All-Purpose Wipers
<b>UNSPSC:</b>	24141506

# Technical Information

**Warnings & Restrictions:**  
Chemical Resistance  
Limited chemical-resistance; not suitable for temperatures over 190° F/88° C.

**Technical Documents:**  
(Available at [newpig.com](http://newpig.com))  
Product Data Sheet (PDS)  
Safety Data Sheet (SDS)  
Chemical Compatibility (CCG)



**New Pig**

By Phone:  
**1-855-493-HOGS**

Online:  
**newpig.com**

Email:  
**hothogs@newpig.com**

One Pork Avenue • Tipton PA 16684-0304  
© 2014 New Pig Corporation. All rights reserved.  
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS667 - Pg 3 of 3