

# PIG® Roof Leak Diverter

#TLS465 - 12' x 12'



Stop devastating roof leak damage and protect your people, equipment and inventory with the original diverter. Invented here!

- The original Leak Diverter - invented here and engineered to stop devastating roof leak damage every time, guaranteed
- Hangs easily in problem spots to catch nuisance leaks and channel them to a floor drain or collection container
- Ideal for quick response to avoid downtime after a roof leak or for long-term prevention in leak-prone areas
- Nonpermeable tarp is vinyl coated for strength and durability; resists punctures, UV and mildew for long life
- Pinched corners help funnel liquid toward center for better drainage
- Accepts a standard 3/4" hose connection to channel liquid to floor drain or collection container (hose sold separately)
- Flow rate of 3.33 gallons per minute when used with a 1/2" ID hose
- Heavy D-rings resist tearing and make installation easy
- Need a custom size or solution? Just call 1-800-HOT-HOGS (468-4647)



**New Pig**

By Phone:  
**1-855-493-HOGS**

Online:  
**newpig.com**

Email:  
**hothogs@newpig.com**

One Pork Avenue • Tipton PA 16684-0304  
© 2014 New Pig Corporation. All rights reserved.  
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS465 - Pg 1 of 3

# TLS465 Specifications

|                                 |  |
|---------------------------------|--|
| <b>Use With:</b>                | Roofs  |
| <b>Drainage Hose Included:</b>  | No   |
| <b>Flow Rate:</b>               | 3.33 gal. per Minute   |
| <b>Grommets/D-Rings:</b>        | 16 Grommets and 4 D-Rings  |
| <b>Hanging Straps Included:</b> | No   |
| <b>Hose Connector:</b>          | .75"   |
| <b>Installation Method:</b>     | Hanging Straps   |
| <b>Thickness:</b>               | Clear - 13 mil, Colors - 16 mil  |
| <b>Sold as:</b>                 | 1 each   |
| <b># per Pallet:</b>            | 120  |
| <b>Composition:</b>             | Leak Diverter (Colors) - 67% PVC, 33% Polyester<br>Leak Diverter (Clear) - PVC w/ Polyester Reinforcement<br>D-Rings - Stainless Steel |
| <b>UNSPSC:</b>                  | 24141506   |

# Technical Information

## Warnings & Restrictions:

Chemical Resistance  
Limited chemical-resistance; not suitable for temperatures over 190° F/88° C.

## Technical Documents:

(Available at [newpig.com](http://newpig.com))

Product Data Sheet (PDS)



**New Pig**

By Phone:  
**1-855-493-HOGS**

Online:  
**newpig.com**

Email:  
**hothogs@newpig.com**

One Pork Avenue • Tipton PA 16684-0304  
© 2014 New Pig Corporation. All rights reserved.  
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS465 - Pg 3 of 3