

# PIG® Rectangular Roof Leak Diverter

#TLS553 - 5' x 10'



Stop devastating roof leak damage and protect your people, equipment and inventory with the original diverter. Invented here!

- The original Leak Diverter - invented here and engineered to stop devastating roof leak damage every time, guaranteed
- Long, rectangular shape is ideal for catching leaks or accumulated condensation along cracks, fissures or pipes
- Hangs easily in problem spots to catch nuisance leaks and channel them to a floor drain or collection container
- Ideal for quick response to avoid downtime after a roof leak or for long-term prevention in leak-prone areas
- Nonpermeable tarp is vinyl coated for strength and durability; resists punctures, UV and mildew for long life
- Pinched corners help funnel liquid toward center for better drainage
- Accepts a standard 3/4" hose connection to channel liquid to floor drain or collection container (hose sold separately)
- Flow rate of 3.33 gallons per minute when used with a 1/2" ID hose
- Grommets resist tearing and make installation easy
- Need a custom size or solution? Just call 1-800-HOT-HOGS (468-4647)



**New Pig**

By Phone:  
**1-855-493-HOGS**

Online:  
**newpig.com**

Email:  
**hothogs@newpig.com**

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.  
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS553 - Pg 1 of 3

# TLS553 Specifications

<b>Use With:</b>	Roofs
<b>Drainage Hose Included:</b>	No
<b>Flow Rate:</b>	3.33 gal. per Minute
<b>Grommets/D-Rings:</b>	12 Grommets
<b>Hanging Straps Included:</b>	No
<b>Hose Connector:</b>	.75"
<b>Installation Method:</b>	Hanging Straps
<b>Thickness:</b>	Clear - 13 mil, Colors - 16 mil
<b>Sold as:</b>	1 each
<b># per Pallet:</b>	336
<b>Composition:</b>	Leak Diverter (Colors) - 67% PVC, 33% Polyester Leak Diverter (Clear) - PVC w/ Polyester Reinforcement
<b>UNSPSC:</b>	24141506

# Technical Information

## Warnings & Restrictions:

Chemical Resistance  
Limited chemical-resistance; not suitable for temperatures over 190° F/88° C.

## Technical Documents:

(Available at [newpig.com](http://newpig.com))

Product Data Sheet (PDS)



**New Pig**

By Phone:  
**1-855-493-HOGS**

Online:  
**newpig.com**

Email:  
**hothogs@newpig.com**

One Pork Avenue • Tipton PA 16684-0304  
© 2014 New Pig Corporation. All rights reserved.  
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS553 - Pg 3 of 3