

Standard features

- Waterproof
- Impact resistant
- Conditional lifetime guarantee
- Crushproof
- Dustproof
- Powerclaw™ latching system
- Soft grip foldable handle
- Lightweight NK-7™ resin
- Padlockable
- 100% stainless steel hardware
- High performance gasket
- Automatic pressure release valve
- Molded-in bezel system
- Integrated lid stay
- Stackable
- Meets airline carry-on regulations

Case specifications

Exterior dimensions	L10.2" x W7.9" x H4.5" L259mm x W201mm x H114mm
Interior dimensions	L8.4" x W6.0" x H3.7" L213mm x W152mm x H94mm
Weight (empty)	1.6 lbs 0.7 kg
Lid depth	0.8" 20mm
Base depth	2.9" 74mm
Material	lightweight NK-7™ resin
Max buoyancy	7 lbs 3.3 kg
Temperature range	Min -20°F (-29°C) Max 140°F (60°C)
Airline carry-on	yes
Watertight (IP67)	yes
Warranty	conditional lifetime guarantee

Available options



Multilayer cubed foam



Waterproof panel kit



Custom foam



Custom printing



TSA approved padlock



Custom adhesive label

Certifications


testing in progress

ATA 300	Impact test
ASTM D4169	Falling rain - Vibration - Drop tests
Mil-STD-810F	Immersion test
IP 67	Ingress protection tests (dust & immersion)

Packaging specifications

Quantity per pack	1
Pack dimensions	L10.4" x W4.7" x H8.3" L264mm x W119mm x H211mm
Pack weight (no foam)	1.9 lbs 0.9 kg

Available colors



Masterpack specifications

Items per masterpack	10
Masterpack dimensions	L19.6" x W12.4" x H14.9" L498mm x W315mm x H378mm
Masterpack weight	20.3 lbs 9.4 kg