

Nashua[®]
TAPE PRODUCTS **FSK**
Foil/Scrim/Kraft Insulation Tape



Nashua® FSK

TAPE PRODUCTS

Foil/Scrim/Kraft Insulation Tape



NASHUA® FSK FOIL/SCRIM/KRAFT TAPE

48mm x 46M
ITEM NO. 652008B
24 rolls/case
27 cases/pallet
UPC: 7-42366-00404-8

72mm x 46M
ITEM NO. 652009B
16 rolls/case
27 cases/pallet
UPC: 7-42366-00094-1

FOR MORE INFORMATION ON
NASHUA® FSK OR OTHER NASHUA®
BRAND PRODUCTS FOR THE HVAC
MARKET, CONTACT YOUR AREA SALES
REPRESENTATIVE.

Berry Plastics Corporation, the industry leader for innovative materials for HVAC, is proud to offer **Nashua® FSK** Foil/Scrim/Kraft Insulation Tape. Formulated with a high performance, high tack rubber adhesive, **Nashua® FSK** meets the needs of virtually all duct sealing and insulation jacketing applications, including vapor barrier sealing on FSK insulation, duct wrap and fiberglass duct board.

SPECIAL FEATURE

- Excellent “quick-stick” and strong adhesion to most surface
- UL 723 Classified
- Resists UV, Humidity and Mold
- Provides long-term anchorage and a durable seal
- Eco-Friendly release liner made from unbleached natural kraft paper
- Low VOC content
- Can contribute toward EA Credit 1 (Optimize Energy Performance and EQ Credit 4.1 (Low Emitting Materials, Adhesives and Sealants) under LEED®

Thickness: 8.0 mils (203.2 μ)

Adhesion to Steel: 70 oz/in (7.66 N/cm)

Tensile Strength: 35 lb/in (61.29 N/cm)

Installation Temperature: 40 to 120° F (4 to 49° C)

Operating Temperature: 40 to 200° F (4 to 93° C)

VOC Content: <1 g/L



Visit our website
to learn more!

For more information:
25 Forge Parkway
Franklin, MA 02038
Phone 508.918.1600 • Fax 508.918.1901
Toll Free US: 1.800.343.7875

 TM
tapes.berryplastics.com