

# Reduce Fire Risks!



*Ideal for any cleaning or wiping operation*

**Justrite® Oily Waste Cans** minimize the risk of a major fire hazard — spontaneous combustion of rags and cloths soaked with solvents, thinners, linseed oil, combustible adhesives and other flammable liquids.

### An Inexpensive Safety Policy

Steel waste cans with self-closing lids — like the Justrite® Oily Waste Can — are designed in compliance with OSHA 29CFR 1910.125. Ours have also undergone rigorous tests and quality audits to obtain UL listing and FM approvals.

Long-lasting Justrite Oily Waste Cans with self-closing lids reduce oxygen required for combustion. They protect your shop or jobsite from fires that can start from:

- spontaneous combustion
- spark
- careless use of smoking materials

Review fire safety with employees — insist they dispose of oily rags and wipes in proper receptacles. Empty daily in the manner advised by your local fire authorities.



## Fully Certified



**100% Leak Tested**



(over)



# JUSTRITE® Product

# Popular!

# ESSENTIALS

## Oily Waste Cans

### Stop fires before they start!

Essential wherever solvent soaked rags and wipes are used, OSHA compliant Oily Waste Cans reduce the risk of fires caused by spontaneous combustion. Sleek steel design with sturdy foot pedal offers effortless, hands-free opening. Unique raised, flow-through base with air ports circulates air and disperses heat. Self-closing cover opens to no more than 60 degrees per FM requirements, and gravity closes to reduce oxygen and prevent fire. One-piece cover facilitates use of disposal collection bags and features a large, swinging carry handle for portability. New SoundGard™ lid option incorporates a specially designed, sound muffling pad to significantly reduce lid closure noise while maintaining FM and UL listings. SoundGard™ is ideal for any setting where it's desirable to minimize disruptive or annoying noise and provide a more comfortable working environment.

Meets OSHA.  
FM approved. UL listed.  
10-year warranty.



Self-closing cover reduces oxygen source to prevent fire from starting.

Swinging carry handle for portability.

Rugged, galvanized steel body features leaktight design.

Fire tested and approved.

Durable powder paint finish for long life.

Trilingual safety label reduces miscommunication.

Round construction and raised, flow-through base with air ports disperse heat.

Popular foot-operated models leave hands free.

Cover gravity closes when pedal is released.

Treadle style pedal for easy opening

One piece lid design facilitates use of disposal collection bags.



100% Leak Tested

Backed by our  
**10 Year**  
Limited Warranty

Foot Operated Oily Waste Cans					With SoundGard™		
Capacity	Dimensions Outer Dia. x H (mm)	Approx./Lstg. Regulation	Red Model No.	Yellow Model No.	Red Model No.	Silver Model No.	Ship Wt. Lbs./Kgs.
6 gallon/23 litre	117/8" x 157/8" (302 x 403)	FM,UL	09100	09101	09108	09104	10/5
10 gallon/38 litre	1315/16" x 181/4" (354 x 464)	FM,UL	09300	09301	09308	09304	12/5
14 gallon/53 litre	161/16" x 201/4" (408 x 514)	FM,UL	09500	09501	09508	09504	15/7
21 gallon/79 litre	183/8" x 237/16" (467 x 595)	FM,UL	09700	09701	09708	09704	22/10

A variety of sizes and styles accommodates your specific need. Choose red, yellow or silver when color identification is desired to help segregate materials or to differentiate department sites.

Hand Operated Oily Waste Cans					Ship Wt.
Capacity	Dimensions Outer Dia. x H (mm)	Approx./Lstg. Regulation	Red Model No.	Yellow Model No.	
2 gallon/8 litre countertop	95/8" x 91/8" (244 x 232)	FM	09200	09200Y	6/3
6 gallon/23 litre	117/8" x 157/8" (302 x 403)	FM,UL	09110	09111	9/4
10 gallon/38 litre	1315/16" x 181/4" (354 x 464)	FM,UL	09310	09311	11/5
14 gallon/53 litre	161/16" x 201/4" (408 x 514)	FM,UL	09510	09511	15/7
21 gallon/79 litre	183/8" x 237/16" (467 x 595)	FM,UL	09710	09711	20/9



New! Silver with SoundGard™

Hand Lift Model #09110 and countertop #09200

Model #09104 and 09301

Foot Operated Models from left to right #09100, 09300, 09500 and 09700

© 2007 JUSTRITE MFG CO.



Mixed Sources

Product group from well-managed forests, controlled sources and recycled wood or fiber.



Phone: 800-798-9250  
Fax: 800-488-5877  
www.justritemfg.com

(over)