

**NYLON - BRAID**

DIAMETER			LENGTH		AVG BREAK	LINEAR DENSITY		WEIGHT	
IN	MM	CIRC	FT	M	STRENGTH	LBS/100'	KTEX	LBS	KG
3/8"	10	1 1/8"	500'	152.4	2475	3.20	47.63	16.0	7.26