

Product Data

- Material: ePTFE/Graphite with an inert lubricant
- Construction: Interwoven™ braid
- Temperature Limit: -400°F to 550°F (-240°C to 288°C)
- pH Range: 0 – 14 (all fluids except strong oxidizers in the 0-2 pH range, such as oleum, fluorine, fuming nitric acid and aqua regia)
- Shaft Speed: 3800 fpm (19.3 m/s)
- Pressure: 1900 psi (131 bar)



Service

Palmetto style 1382 is a lower cost alternative to 1389 (stenciled 100% GFO®) that will not harm shaft sleeves. Excellent heat dissipation prevents glazing and scoring, increasing packing and sleeve service life. In addition, less energy is used to turn the shaft and a lower leak-off may be attained.

Typical Applications

1382 is recommended for rotating pumps and valves in virtually any chemical or abrasive slurry. It is an excellent choice for sludge, paper, chemical and mining pumps. Especially effective in asphalt pumps.

How to Order

Specify: style number, size, quantity and packaging desired

Size	in	1/8"	3/16"	1/4"	5/16"	3/8"	7/16"	1/2"	9/16"	5/8"	11/16"	3/4"	13/16"	7/8"	15/16"	1"
	mm		3,20	4,80	6,40	7,90	9,50	11,10	12,70	14,30	15,90	17,50	19,10	20,60	22,20	23,80
Length	ft/lb	62.48	44.47	26.24	15.53	10.10	7.72	5.79	4.78	3.95	3.50	2.79	2.40	2.12	1.90	1.63
	M/kg	41,86	29,79	17,50	10,40	6,76	5,17	3,80	3,20	2,64	2,34	1,86	1,60	1,42	1,27	1,09
Packaging	*Sizes 1/8" through 1/2" available in 1 lb. spools. All sizes available in 5 and 10 lb. boxes; 25 and 50 lb. reels.															

Distributed by

A Greene, Tweed Company
 Denton Industrial Park
 25 Engerman Ave., Denton, MD 21629
 Phone: +1.410.479.2244, Fax: +1.410.479.0836
 E-mail: info@palmettopackings.com
 Website: www.palmettopackings.com

