

DRY ICE TRANSPORT STORAGE CHESTS

THERMO CHILL® Durable “Indestructible” Transport



DRY ICE TRANSPORT CHEST

Thermo Chill® indestructible transporters maintain critical temperatures for your perishable materials. These durable transports are tough, double walled and built to last. Made using special melt-blend, high impact plastic, that is filled with polyurethane foam. Each container resists cold impacts and provides longer cold retention. Unlike other products, these transporters do not contain any fiberglass insulation and are, therefore, preferred by laboratories. All sizes and styles have superior insulation for lowest sublimation rates. The tight fitting lids and durable construction maintain temperatures across a wide range of ambient temperatures. These containers have a square interior for maximum space utilization and a smooth interior that is easy to clean.

PART #	INSIDE DIMENSIONS L x W x D	OUTSIDE DIMENSIONS L x W x D	CUBIC FEET	WEIGHT
TC02	21" x 11" x 14"	30" x 21" x 24"	2	45 lbs.
TC05	24" x 12" x 29"	30" x 18" x 37"	5	58 lbs.
TC11*	33" x 20" x 27"	42" x 28" x 40"	11	130 lbs.
TC30	42" x 36" x 32"	49" x 43" x 43"	30	220 lbs.

* Caster Wheel Model.

COOL BARRIER BUBBLE



Quickly convert any stock box into an economical reflective thermal insulated shipper.

- Provides overnight protection.
- Space saving liners stores flat (Light Duty).
- Leak resistant
- Use with ICE-BRIX® cold packs for extended shipping.

Visit www.polar-tech.com for our complete line of shipping products, labels and more containers to help with your dry ice needs.