

PROTO® LOCKING PLIERS



- Locking mechanism helps leave both hands free when clamping, helping to eliminate squeezing action and general hand fatigue when manipulating.
- Tip of release lever projects at end of handle for a quick, no-pinch, powerful release especially when tools are firmly locked.
- Spring loaded release lever is out of the way when handling.
- Drop forged jaws and rugged tooth profile for durability and toughness.
- Holes in mobile jaw are drilled and not press punched to ensure they are cylindrical to ensure maximum bearing with rivets. (Punched holes tend give poor bearing.)
- Large diameter of rivets to help permit secure joints adding to the durability and robustness of the tools.
- Piano wire spring for smooth and efficient jaw opening.

PROTO GRIP HOLDERS (JGHXL, JMGHXL)

- Designed with special slot.
- Swivel pad.
- Butterfly screw.
- Firmly holds 10" tools converting them into a versatile portable vise.
- Helps ensure firm hold on all workpieces.
- Easy to adjust.
- Use a standard c-clamp or combined with locking tools for a hands free work.

PROTO OPTIMUM GRIP PLIERS (J280XL, J281XL)

- Jaw configuration combining straight, curved and convex profiles.
- Versatile tool securely gripping round, flat and large objects.
- Multi-use for plumbers, welders and others.

PROTO CURVED JAW PLIERS (J290XL, J292XL)

- Narrow large opening curved shaped jaws.
- Allows firm hold on all round shapes.
- Universal tool for multi-use.

PROTO STRAIGHT JAW PLIERS (J291XL, J293XL)

- Heavy duty nose.
- Reinforced precisely machined teeth.
- Strong, tough tool.
- Helps provide secure grip for extra tough jobs.
- General purpose for various maintenance situations.

PROTO CURVED WITH CUTTER PLIERS (J292WRXL, J293WRXL, J294WRXL)

- Wide jaw profile with wire cutter.
- Two tools in one!
- Multi-functional use.

Product SKU No.	Description	UIC	Length	Jaw Opng.	Jaw Wdth.	Jaw Depth	Wght. (lbs.)	Jaw Hardness
JGHXL	Proto Grip Holder	662679997175	5-5/32"	—	—	1"	0.55	—
JMGHXL	Proto Grip Holder	662679997182	5-5/32"	—	—	1"	0.66	—
J280XL	Proto Optimum Grip Pliers - 7-7/8"	662679997205	7-7/8"	1-9/16"	27/64"	1-25/32"	0.90	49-53
J281XL	Proto Optimum Grip Pliers - 9-27/32"	662679997212	9-27/32"	2-23/64"	1/2"	2-5/32"	1.43	49-53
J290XL	Proto Curved Jaw Pliers - 7-15/32"	662679997083	7-15/32"	1-21/32"	11/32"	1-19/64"	0.82	49-53
J292XL	Proto Curved Jaw Pliers - 9-1/4"	662679997106	9-1/4"	2-23/64"	25/64"	1-1/2"	1.32	49-53
J291XL	Proto Straight Jaw Pliers - 7-15/32"	662679997151	7-15/32"	1-21/32"	1/2"	1-1/2"	0.88	49-53
J293XL	Proto Straight Jaw Pliers - 9-1/4"	662679997120	9-1/4"	2-23/64"	5/8"	1-21/32"	1.39	49-53
J292WRXL	Proto Curved Jaw w/Cutter Pliers - 9-4/11"	662679997113	9-4/11"	2-23/64"	1/2"	1-1/2"	1.32	49-53
J293WRXL	Proto Curved Jaw w/Cutter Pliers - 5-1/2"	662679997137	5-1/2"	1-19/64"	21/64"	55/64"	0.40	49-53
J294WRXL	Proto Curved Jaw w/Cutter Pliers - 7-15/32"	662679997144	7-15/32"	1-21/32"	11/32"	1-11/64"	0.82	49-53
J282XL	Proto Grooved Grip Pliers	662679997229	9-7/16"	2-23/64"	1/2"	1-25/32"	1.32	49-53
J289LNXL	Proto Long Nose Pliers	662679997076	9-1/32"	2-3/4"	25/64"	2-9/16"	0.88	49-53

PROTO® LOCKING PLIERS



- Locking mechanism helps leave both hands free when clamping, helping to eliminate squeezing action and general hand fatigue when manipulating.
- Tip of release lever projects at end of handle for a quick, no-pinch, powerful release especially when tools are firmly locked.
- Spring loaded release lever is out of the way when handling.
- Drop forged jaws and rugged tooth profile for durability and toughness.
- Holes in mobile jaw are drilled and not press punched to ensure they are cylindrical to ensure maximum bearing with rivets. (Punched holes tend give poor bearing.)
- Large diameter of rivets to help permit secure joints adding to the durability and robustness of the tools.
- Piano wire spring for smooth and efficient jaw opening.

PROTO GROOVED GRIP PLIERS (J282XL)

- Tapered groove in mobile jaw.
- Convex jaw.
- Firm hold of cylindrical objects without lateral movement
- Clears small obstacles.
- Ideal for holding and handling drill bits, taps, fasteners and tubes in general maintenance work.

PROTO LONG NOSE PLIERS (J289LNXL)

- Long slim jaw design.
- Curved section.
- Pliers can reach deep into recessed areas.
- Can hold rounded objects.
- Great for holding, placing and extracting pieces in awkward areas, engines, etc.

Product SKU No.	Description	UIC	Length	Jaw Opng.	Jaw Wdth.	Jaw Depth	Wght. (lbs.)	Jaw Hardness
JGHXL	Proto Grip Holder	662679997175	5-5/32"	—	—	1"	0.55	—
JMGHXL	Proto Grip Holder	662679997182	5-5/32"	—	—	1"	0.66	—
J280XL	Proto Optimum Grip Pliers - 7-7/8"	662679997205	7-7/8"	1-9/16"	27/64"	1-25/32"	0.90	49-53
J281XL	Proto Optimum Grip Pliers - 9-27/32"	662679997212	9-27/32"	2-23/64"	1/2"	2-5/32"	1.43	49-53
J290XL	Proto Curved Jaw Pliers - 7-15/32"	662679997083	7-15/32"	1-21/32"	11/32"	1-19/64"	0.82	49-53
J292XL	Proto Curved Jaw Pliers - 9-1/4"	662679997106	9-1/4"	2-23/64"	25/64"	1-1/2"	1.32	49-53
J291XL	Proto Straight Jaw Pliers - 7-15/32"	662679997151	7-15/32"	1-21/32"	1/2"	1-1/2"	0.88	49-53
J293XL	Proto Straight Jaw Pliers - 9-1/4"	662679997120	9-1/4"	2-23/64"	5/8"	1-21/32"	1.39	49-53
J292WRXL	Proto Curved Jaw w/Cutter Pliers - 9-4/11"	662679997113	9-4/11"	2-23/64"	1/2"	1-1/2"	1.32	49-53
J293WRXL	Proto Curved Jaw w/Cutter Pliers - 5-1/2"	662679997137	5-1/2"	1-19/64"	21/64"	55/64"	0.40	49-53
J294WRXL	Proto Curved Jaw w/Cutter Pliers - 7-15/32"	662679997144	7-15/32"	1-21/32"	11/32"	1-11/64"	0.82	49-53
J282XL	Proto Grooved Grip Pliers	662679997229	9-7/16"	2-23/64"	1/2"	1-25/32"	1.32	49-53
J289LNXL	Proto Long Nose Pliers	662679997076	9-1/32"	2-3/4"	25/64"	2-9/16"	0.88	49-53