Digital Programmable Wall Heater

- ► 5/2 DAY PROGRAMMABLE THERMOSTAT
- ► LED TOUCH SCREEN OPERATION WITH ADJUSTABLE SOUND
- ► AUTOMATIC ADJUSTABLE WATTAGE OUTPUT
- ► TWO GRILLE COLORS AVAILABLE, GRAY (STANDARD) & NORTHERN WHITE
- ► FAN ONLY MODE
- ► CONVENIENT REMOTE CONTROL INCLUDED
- **► 5 YEAR ELEMENT WARRANTY**









► APPLICATIONS INCLUDE:

- DENS
- BASEMENTS
- BATHROOMS
- BEDROOMS
- OFFICES
- ... AND MUCH MORE








SELECTION CHART

CATALOG NUMBER	UPC	VOLTS	WATTS	AMPS	BTUHR	WIRE Size
HT2024SS	6 85360 15351 3	240	250 - 2000	1.0 - 8.3	853 - 6826	14
HT1502SS	6 85360 15350 6	120	200 - 1500	1.6 - 12.5	682 - 5120	12


Note: Standard grille color is gray. Add NW suffix for Northern White.

SMHTSSNW	6 85360 15631 6	Northern White Surface Mounting frame 14-5/8"W X 20-1/4"H X 3-3/4"D		
SMHTSSBL	6 85360 15630 9	Black Surface Mounting frame 14-5/8"W X 20-1/4"H X 3-3/4"D		

THERMOSTAT DISPLAY



DIMENSIONS



FEATURES

- Heater automatically adjusts wattage output and blower speed resulting in whisper quiet operation for optimum comfort.
- Heating element is heavy duty non-glowing steel fins brazed to steel sheathed tubular elements in a grid pattern that covers the entire discharge area.
- Built-in fan delay operates when unit is turned off after heating to prolong element life.
- ► 5/2 day electronic programmable built-in thermostat adaptable to fit any life style while providing energy savings and precise temperature performance.
- ► Easy to use LED touch screen operation.
- Convenient remote control included.
- Contemporary, clean design with night light feature complements any decor.
- Two grille colors to choose from, Gray (standard) and Northern White.
- Designed for easy installation. Heater is mounted prior to wiring. Both hands are free to make field connections in roomy compartment.
- This heater is designed for installation in 2 x 4 frames or larger wall sections using the wall box provided.
- The heater may be wired with standard building wire (60°C). Refer to specification chart for correct supply voltage and wire size.

MOUNTING LIMITATIONS

Do not install heater closer than 12" to the floor, 12" to an adjacent wall, 36" to the ceiling.

Do not install heater behind towel rack or door, upside down or sideways, in the floor, ceiling, or in closets.

HEATER REMOTE

An easy to use remote control is included to provide convenient heat and power adjustment from up to 12 feet away. Heater must be in direct line of sight to operate correctly. Unit can be controlled with or without remote control.

