



# Rittal – The System.

Faster – better – everywhere.

## Rittal Corporation – Climate Control Products

Rittal's array of climate control options offers energy-efficient, economical solutions for a variety of situations whether you're tasked with cooling or heating. From filter fans to complex air conditioning systems, the cooling components represents world-class technology. Air conditioners utilize an innovative nano-coating applied to the condenser coils — enhancing performance while cutting energy usage and costs by as much as 40% and reducing carbon emissions by up to 2,000 lbs. per unit, per year. This high-tech approach that can reduce maintenance demands and extend the life the unit. Filter fans are available in an assortment of sizes and configurations and heaters can be installed with or without fans in ranges from as low as 34 BTU to as high as 2,730 BTU.

### Filter Fans and Accessories

Grainger No.	Rittal No.	Description
6YDK8	3238.110	Filter Fan, 39 CFM 115 V, 50/60 Hz
6YDL5	3238.100	Filter Fan, 39 CFM 230 V, 50/60 Hz
6YDN2	3238.124	Filter Fan, 32 CFM 24 V DC
6YDN8	3238.200	Outlet Exhaust Louver for 3238
2PVE7	3322.700	Filter Mat (Std) for 3238
6YDK9	3239.110	Filter Fan, 71 CFM 115 V, 50/60 Hz
6YDL6	3239.100	Filter Fan, 71 CFM 230 V, 50/60 Hz
6YDN3	3239.124	Filter Fan, 62 CFM 24 V DC
6YDN9	3239.200	Outlet Exhaust Louver for 3239
2PVF3	3171.100	Filter Mat (Std) for 3239
6YDL1	3241.110	Filter Fan, 147 CFM 115 V, 50/60 Hz
6YDL8	3241.100	Filter Fan, 147 CFM 230 V, 50/60
6YDN5	3241.124	Filter Fan, 135 CM 24 V DC
6YDP0	3240.200	Outlet Exhaust Louver for 3241
2PVF8	3172.100	Filter Mat (Std) for 3241
6YDL2	3243.110	Filter Fan, 353 CFM 115 V, 50/60 Hz
6YDL9	3243.100	Filter Fan, 353 CFM 230 V, 50/60 Hz
6YDP1	3243.200	Outlet Exhaust Louver for 3243
2PVG3	3173.100	Filter Mat (Std) for 3243

### Thermoelectric Cooler

Grainger No.	Rittal No.	Description
6YDP4	3201.200	Thermoelectric cooler, 340 BTU, 110-230V
6YDP5	3201.300	Thermoelectric cooler, 340 BTU, 24V DC

### Heater, 110 – 240 V, 50/60 Hz w/o Fan, Continuous Thermal Output 34 – 512 BTU

Grainger No.	Rittal No.	Description
6YDJ3	3105.310	5 x 2 x 2, 27 – 34 BTU
6YDJ4	3105.320	5 x 2 x 2, 61 – 68 BTU
6YDJ5	3105.330	6 x 3 x 2, 78 – 102 BTU
6YDJ6	3105.340	6 x 3 x 2, 167 – 170 BTU
6YDJ7	3105.350	9 x 3 x 2, 215 – 256 BTU
6YDJ8	3105.360	6 x 4 x 3, 293 – 341 BTU
6YDJ9	3105.370	7 x 4 x 3, 444 – 512 BTU

### Heater, 110 V with Fan, Continuous Thermal Output 853 – 2730 BTU

Grainger No.	Rittal No.	Description
49C122	3105.410	8 x 4 x 4, 853 BTU
49C123	3105.420	8 x 4 x 4, 1365 BTU
49C124	3105.430	8 x 4 x 4, 2730 BTU

### Heater, 230 V with Fan, Continuous Thermal Output 853 – 2730 BTU

Grainger No.	Rittal No.	Description
49C125	3105.380	8 x 4 x 4, 853 BTU
49C126	3105.390	8 x 4 x 4, 1365 BTU
49C127	3105.400	8 x 4 x 4, 2730 BTU



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Rittal Corporation – Climate Control Products

## NEMA 12 TopTherm Plus Wallmount Air Conditioner

Grainger No.	Rittal No.	Description
2PUX6	3302.110	1090 BTU, 115V, 60Hz
2PUX7	3302.100	1090 BTU, 230V, 60Hz,
2PUX8	3303.510	2080 BTU, 115V, 60Hz
2PUX9	3303.500	2080 BTU, 230V, 60Hz
2PUY1	3361.510	2664 BTU, 115V 50/60Hz
2PUY2	3361.500	2664 BTU 230V 50/60Hz
2PUY3	3304.510	3600 BTU, 115V, 60Hz
2PUY4	3304.500	3600 BTU, 230V, 60Hz
2PUY5	3304.540	3600 BTU, 460V 3~, 60Hz
2PUY6	3305.510	5150 BTU, 115v, 60Hz
2PUY7	3305.500	5150 BTU, 230V, 60Hz
2PUY8	3305.540	5150 BTU, 460V 3~, 60Hz
2PUY9	3328.510	8000 BTU 115V 60Hz
2PUZ1	3328.500	8000 BTU 230V 60Hz
2PUZ2	3328.540	8000 BTU 460V 3~ 60Hz
2PUZ3	3329.510	9390 BTU 115v 60Hz
2PUZ4	3329.500	9390 BTU 230V 60Hz
2PUZ5	3329.540	9220 BTU 460V 3~ 60Hz
2PUZ6	3332.540	15000 BTU 460V 3~ 60Hz

## NEMA 12 TopTherm Plus Roofmount Air Conditioner

Grainger No.	Rittal No.	Description
2PUZ7	3382.510	1740 BTU 115V 60Hz
2PUZ8	3382.500	1740 BTU 230V 60Hz
2PUZ9	3383.510	3680 BTU 115V 60Hz
2PVA1	3383.500	3680 BTU 230V 60Hz
2PVA2	3384.510	5200 BTU 115V 60Hz
2PVA3	3384.500	5200 BTU 230V 60Hz
2PVA4	3385.510	7270 BTU 115V 60Hz
2PVA5	3385.500	7270 BTU 230V 60Hz
2PVA6	3386.540	11250 BTU 460V 3~ 60Hz
2PVA7	3387.540	14300 BTU 460V 3~ 60Hz

## NEMA 4X TopTherm Plus Wallmount Air Conditioner

Grainger No.	Rittal No.	Description
2PVA8	3303.514	1800 BTU, 115V, 60Hz
2PVA9	3303.504	1800 BTU, 230V, 60Hz
2PVC1	3304.514	3600 BTU, 115V, 60Hz
2PVC2	3304.504	3600 BTU, 230V, 60Hz
2PVC3	3304.544	3600 BTU, 460V ~3, 60Hz
2PVC4	3305.514	5150 BTU, 115v, 60Hz
2PVC5	3305.504	5150 BTU, 230v, 60Hz
2PVC6	3305.544	5150 BTU, 460v ~3, 60Hz
2PVC7	3328.514	8000 BTU, 115v, 60Hz
2PVC8	3328.504	8000 BTU, 230v, 60Hz
2PVC9	3328.544	8000 BTU, 460v ~3, 60Hz
2PVD1	3329.514	9390 BTU, 115v, 60Hz
2PVD2	3329.504	9390 BTU, 230v, 60Hz
2PVD3	3329.544	9220 BTU, 460v ~3, 60Hz

## Filter Mat for Air Conditioners

Grainger No.	Rittal No.	Description
2PVD4	3286.300	Foam Filter for 3302/3303
2PVD5	3286.310	Metal Filter for 3302/3303
2PVD6	3286.400	Foam Filter for 3305/3328/3329/3332
2PVD7	3286.410	Metal Filter for 3305/3328/3329/3332
2PVD8	3286.500	Foam Filter for 3382/3383/3384/3385
2PVD9	3286.510	Metal Filter for 3382/3383/3384/3385
2PVE1	3286.600	Foam Filter for 3386/3387
2PVE2	3286.610	Metal Filter for 3386/3387

## Accessories

Grainger No.	Rittal No.	Description
2PVG4	3110.000	Thermostat 24-230V AC/DC
2PVG5	4127.010	Door Switch with Fixing Kit
6YDK6	3118.000	Hygrostat, 24-230V

