

PATCH IT



Low odor, easy maintenance, concrete patching solutions



	BlokFil™	5499 Patching Compound	5494 TurboKrete®
	2 component, 100% solids epoxy based concrete and masonry void and crack filler/patching compound.	2 component, high solids epoxy patching compound.	5494 TurboKrete® 3 component trowel applied epoxy mortar.
Patch Size	Up to 7/16" deep and 1½" wide Vertical or horizontal surfaces	Up to 2" deep for horizontal and maximum 1/4" - 3/8" depth for vertical applications	No limitations on width, up to 8" deep. Not recommended for vertical applications.
Surface Preparation	Clean and free of grease, oil, existing sealers, paint and other contaminants that may cause adhesion problems	Clean and free of grease, oil, existing sealers, paint and other contaminants that may cause adhesion problems	Clean and free of grease, oil, existing sealers, paint and other contaminants that may cause adhesion problems
Application Method & Temps	Steel trowel, rubber float, plaster's knife, putty knife. 65°F-90°F	Putty knife or trowel. 50°F-100°F	Steel trowel. 45°F-90°F
Working Time & Cure Time	10-12 minutes working time. Cure in 1-2 hours. Recoat within 24 hours or scuff sanding required.	50 minutes working time. Tack free in 2-3 hours. Foot traffic in 16 hours. Full cure in 72 hours.	20-30 minutes working time. Foot traffic/recoat in 2-4 hours. Vehicle traffic in 6-8 hours. Full chemical exposure in 3 days.
Performance & Appearance	High impact resistance. Non-porous. Excellent adhesion — exceeds the strength of concrete. Unpigmented, amber color. Smooth finish.	Self-priming. Up to 3 times stronger than concrete. Flat gray. Medium (float) troweled finish.	High resistance to impact. Excellent adhesion — exceeds the strength of the concrete. Dark gray. Semi-smooth troweled finish.
Product Numbers	237321 – Base 237327 – Activator (Order each component separately)	5499499 – 2 Gallon Kit (base and activator included)	5494323 – 0.3 cu ft Kit (3 component base, activator and aggregate included)

PRODUCTS THAT WORK AS HARD AS YOU DO®