

TURBOKRETE®

MULTI-PURPOSE CONCRETE REPAIR AND ADHESIVE



Comes in a convenient 2K cartridge.

Also available: Heavy-duty caulk gun and replacement static mixers.



**The ultimate 100% solids
non-sag epoxy repair.**

- Easy to use — convenient 2K cartridge
- Superior non-sag formula excellent for bridging horizontal or vertical cracks, even under water
- Twice as strong as concrete
- Works on concrete, masonry, brick, steel and more
- Low odor, low VOC



TURBOKRETE®

MULTI-PURPOSE CONCRETE REPAIR AND ADHESIVE

The ultimate 100% solids non-sag epoxy repair

Less Prep Time • Minimal surface prep, maximum adhesion

Less Application Time • Convenient 2K cartridge — 1:1 mix ratio for trowel applications

Less Downtime • Fully cured in 2 hours

Greater Lifetime Value • Twice as strong as concrete — will not soften over time

Typical applications

Interior and exterior concrete or masonry for cracks, spalls and leaks on vertical, horizontal or overhead surfaces. Also great as an adhesive.

Target markets

Concrete Flooring Contractors • Concrete Restoration Contractors • Industrial Plants
DOT-State and Paving Contractors • Manufacturing Plants • Stadiums • Theme Parks

Colors



9 oz. cartridge
#257395

Companion Products



Replacement Static Mixers
(pack of 3) #257397



Heavy-Duty Caulk Gun
#257396



Horizontal Repairs



Vertical Repairs

BASIC DATA	
Color	Concrete Gray
Consistency	Non-sag gel
Gel Time (@ 75°F)	8 minutes
Minimum Load Time	4 hours @ 75°F
Application Temperature Range	35-110°F

TECHNICAL DATA		
PROPERTIES	ASTM	RESULTS
Compressive Strength @ 7 days (65°F)	D695	8,000 psi
Bond Strength @ 2 days	C882	1,130 psi
Bond Strength @ 14 days	C882	1,690 psi
Linear Coefficient of Shrinkage	D2566	.004 cm/cm

APPLICATION:



SUBSTRATES:



CONCRETE



CERAMIC



MASONRY



STEEL



TILE