



Re-Form™ Eco-Friendly Sorbent Products



50% More Absorbent • Lower Cost • Green Eco-Friendly

www.BradyID.com/spc



Made In The U.S.A



Re-Form™
Eco-Friendly Sorbents

■ **Better Absorbency**

Re-Form sorbents have been tested to be 25-50% more absorbent than oil-based polypropylene sorbents, so you'll use less product to get the job done.

UP TO
**50%
MORE
ABSORBENT**

■ **Cost Savings**

More absorbency means less waste and greater cost savings. Plus many Re-Form sorbents are less expensive than our polypropylene sorbents. We also guarantee stable pricing on Re-Form sorbents because the price of Re-Form sorbents is not impacted by volatile oil prices.

■ **Green to produce. Green in use.**

Re-Form sorbents are made from a minimum of 80% recycled newsprint (Universal) or cotton/cellulose (Oil Only)...unlike oil-based polypropylene sorbents. And Re-Form's better absorbency means you'll have less sorbent material to dispose of.

Re-Form Guarantee

- Guaranteed price stability
- Money back guarantee on your initial case

■ **Supports Corporate Sustainability and LEED Initiatives**

■ **Class A Fire Retardant**

Universal Re-Form™ sorbents meet NFPA Class A Fire retardancy.



Request A Catalog

Sorbent & Spill Containment Catalog available at: www.BradyID.com/spc

Safety Catalog available at: www.BradyID.com

An Eco-Friendly Family Of High-Performance Sorbents:



Re-Form

Universal sorbent made from recycled newsprint and cellulose.

- Netted construction
- Quick clean up for drips and spills
- Indoor or dry weather outdoor use



Re-Form Plus

Same as Reform Universal with abrasion resistant coverstock on one side.

- Perfect around machines and equipment with moderate foot traffic
- Spunbound coverstock on 1 side
- Indoor use or dry weather outdoor use



Re-Form XPlus

Same as Reform Universal with tough abrasion resistant coverstock on two sides for extra durability.

- Spunbound coverstock on 2 sides
- Ideal for foot traffic and wiping applications
- Indoor use or dry weather outdoor use



Re-Form Oil Only

Oil Only sorbent made from 80% cotton-cellulose; a renewable resource. Absorbs petroleum based liquids, grease, transmission fluids and coolant.

- Great for outdoor oil/fuel storage area
- Durable spunbound coverstock on 2 sides for pads, and on 1 side for rolls
- Repels water and floats - ideal for marine applications and spills
- Available in weather resistant bags



**Re-Form™ Sorbents are not intended for use with highly aggressive chemicals.*



Re-Form™ Pads

Part #	Description	Size	Absorbency: Gal./Case	Qty/ Case	Pallet Qty.	Ship Wt. (lbs)
Re-Form						
RF100	Re-Form Heavy WT. Pad	15" x 19" (38.1 x 48.3cm)	40 (151L)	100	24	19.0
RF300	Re-Form Medium WT. Pad	15" x 19" (38.1 x 48.3cm)	32 (121L)	100	30	14.8
RF500	Re-Form Light WT. Pad	15" x 19" (38.1 x 48.3cm)	24 (90L)	100	36	12.0
Re-Form Plus (1-side coverstock)						
RFP100	Re-Form Plus Heavy WT. Pad, Perforated	15" x 19" (38.1 x 48.3cm)	40 (151L)	100	24	19.5
RFP300	Re-Form Plus Medium WT. Pad, Perforated	15" x 19" (38.1 x 48.3cm)	32 (121L)	100	30	16.0
RFP500	Re-Form Plus Light WT. Pad, Perforated	15" x 19" (38.1 x 48.3cm)	24 (90L)	100	36	12.7
Re-Form XPlus (2-side coverstock)						
RFDP300	Re-Form XPlus Medium WT. Pad	15" x 19" (38.1 x 48.3cm)	32 (121L)	100	30	16.6
Re-Form Oil Only (2-side coverstock)						
RFODP100-B	Re-Form Oil Only Heavy WT. Pad, Perforated	15" x 19" (38.1 x 48.3cm)	39 (148L)	100/bag	18	10.0
RFODP100	Re-Form Oil Only Heavy WT. Pad, Perforated	15" x 19" (38.1 x 48.3cm)	39 (148L)	100	24	12.0



Re-Form™ Rolls

Part #	Description	Size	Absorbency: Gal./Case	Qty/ Case	Pallet Qty.	Ship Wt. (lbs)
Re-Form Plus (1-side coverstock)						
RFP14P	Re-Form Plus Heavy WT. Roll, Perforated	14.25" x 150' (36.2cm x 45.7m)	30 (113L)	1	24	15.5
RFP28-DP	Re-Form Plus Heavy WT. Roll, Dbl Perf'ed	28.5" x 150' (72.4cm x 45.7m)	62 (234L)	1	12	33.0
RFP314P	Re-Form Plus Medium WT. Roll, Perforated	14.25" x 150' (36.2cm x 45.7m)	29 (109L)	1	24	15.5
RFP328-DP	Re-Form Plus Medium WT. Roll, Dbl Perf'ed	28.5" x 150' (72.4cm x 45.7m)	53 (200L)	1	12	30.5
Re-Form XPlus (2-side coverstock)						
RFDP314P	Re-Form XPlus Medium WT. Roll	14.25" x 150' (36.2cm x 45.7m)	27.5 (104L)	1	24	16.7
RFDP328-DP	Re-Form XPlus Medium WT. Roll	28.5" x 150' (72.4cm x 45.7m)	55 (208L)	1	12	33.3
Re-Form Oil Only (1-side coverstock)						
RFOP14P	Re-Form Oil Only Heavy WT. Roll, Perforated	14.25" x 150' (36.2cm x 45.7m)	37 (141L)	1	24	10.5
RFOP28-DP	Re-Form Oil Only Heavy WT. Roll, Dbl Perf'ed	28.5" x 150' (72.4cm x 45.7m)	74 (282L)	1	12	21.0



Re-Form™ SOCS

Part #	Description	Size	Absorbency: Gal./Case	Qty/ Case	Pallet Qty.	Ship Wt. (lbs)
Multiwick SOCS						
MS-50	Re-Form Multiwik Soc	3" x 4' (76mm x 1.2m)	40 (151L)	40	15	43.0
MS-412	Re-Form Multiwik Soc	3" x 4' (76mm x 1.2m)	12 (45L)	12	42	12.0
MS-806	Re-Form Multiwik Soc	3" x 8' (76mm x 2.4m)	12 (45L)	6	42	12.0
MS-124	Re-Form Multiwik Soc	3" x 12' (76mm x 3.6m)	12 (45L)	4	42	12.0
Re-Form Oil Only SOCS						
RFO412	Re-Form Oil Only Soc	3" x 4' (76mm x 1.2m)	15 (56L)	12	42	10.5

Free On-Site Sorbent Survey

Brady-SPC will visit your site, analyze your sorbent usage and create a customized report recommending:

- Cost savings, reduced usage / proper usage for your application
- Sorbent standardization & consolidation
- Compliance with OSHA, EPA and SPCC regulations



Re-Form™ Spill Kits

Accidents happen. Be prepared with Re-Form Eco-Friendly Emergency Response Spill Kits. Designed to help companies meet SPCC compliance, Re-Form Spill Kits provide a quick and easy solution for spill response. They offer 24% more absorbency and 5% savings over standard polypropylene spill kits.



Part Number: SKR-PP

Re-Form Economy Spill Kit

- Packed in a bright water-resistant safety yellow bag that is easy to carry and store
- Ideal kit for small spills
- Helps comply with 40 CFR 263 regulations

Contains:

- 10 RF100 (15" x 19") Pads
- 2 MS412 (3" x 4') Socs
- 1 pair of Nitrile gloves
- 1 6mil disposal bag
- 1 Instruction sheet



Part Number: SKR-ATK

Re-Form Attack Pac Spill Kit

- Packed in a puncture and UV-resistant foil bag that is easy to carry, hang and store
- Ideal kit for small spills
- Helps comply with 40 CFR 263 regulations

Contains:

- 15 RF100 (15" x 19") Pads
- 3 MS412 (3" x 4') Socs
- 1 pair of goggles
- 1 pair of Nitrile gloves
- 1 6mil disposal bag
- 1 Instruction sheet



Part Number: SKR-20

Re-Form 20 Gallon Lab Pack

- Packed in a UN-approved water and chemical-resistant Lab Pack container with screw top lid
- Ideal kit for small to medium spills
- Helps comply with 40 CFR 263 and 49 CFR 173 regulations

Contains:

- 12 RF100 (16" x 20") Pads
- 3 MS124 (3" x 12") Socs
- 2 AW1818 (18" x 18") Pillows
- 1 pair of goggles
- 1 pair of Nitrile gloves
- 3 6mil disposal bags
- 1 Emergency Response Handbook



Part Number: SKR-55

Re-Form 55 Gallon Spill Drum

- Packed in a UN-approved water and chemical resistant, lever locked lid container
- Ideal kit for medium spill response
- Helps comply with 40 CFR 263 and 49 CFR 173 regulations

Contains:

- 50 RF100 (16" x 20") Pads
- 4 MS124 (3" x 12") Socs
- 8 AW1818 (18" x 18") Pillows
- 1 pair of goggles
- 1 pair of Nitrile gloves
- 5 6mil disposal bags
- 1 Emergency Response Handbook
- Lever locked lid with UV Shield liner



Part Number: SKR-95

Re-Form 95 Gallon Spill Drum

- Packed in a UN- and DOT-approved water and chemical-resistant, screw top container
- Ideal kit for medium spill response
- Helps comply with 40 CFR 263 and 49 CFR 173 regulations

Contains:

- 110 RF100 (16" x 20") Pads
- 12 MS412 (3" x 4') Socs
- 8 MS124 (3" x 12") Socs
- 8 AW1818 (18" x 18") Pillow
- 1 pair of goggles
- 1 pair of Nitrile gloves
- 10 6mil disposal bags
- 1 Emergency Screw top locked lid
- UV Shield liner under the lid

*Re-Form™ Sorbents are not intended for use with highly aggressive chemicals.

Custom Spill Kits Also Available

Choose from a wide selection of Brady's most popular pads, socs, booms, pillows, safety accessories, and containers to create your own Custom Spill Kit.

With no minimum requirements, Custom Spill Kits give you the flexibility to pick only the products you need without the extra cost of items you don't want.

USA
1-888-272-3946
www.BradyID.com

Canada
1-800-263-6179
www.BradyCanada.ca

Mexico
1-800-262-7777
www.BradyLatinAmerica.com



Y918753 MS918753

© 2010 Brady Worldwide, Inc. All Rights Reserved

 **BRADY**
WHEN PERFORMANCE MATTERS MOST™