

YES!

WE CAN!

With Piano
Hinge

Ready Built 2™

READY-TO-USE!

Ready-Built II Lockers Include:

- ✓ **Assembly**
- ✓ **Padlocks**
- ✓ **Padlock strike plates**
- ✓ **Slope tops**
- ✓ **6" high metal bases**



Single Tier,
1 wide,
1 opening



Double Tier,
1 wide,
2 openings



Triple Tier,
1 wide,
3 openings



Six Tier,
1 wide,
6 openings

Slope Tops

Provide a more finished appearance and prevent items from being placed or stored on locker tops.

Padlocks

Are included for each door. 3-number combinations provide for maximum security. No need to go out and buy locks allowing immediate use of lockers upon arrival. Locks are master keyed.

Strike Plates

Aluminum plates are riveted to door to prevent padlocks from marring painted door finish on six tier.

Closed Metal Base

Front and side bases close off area below lockers at 6" legs to prevent collection of debris.

COLOR SELECTION

729
PARCHMENT (PT)

725
HALLOWELL GRAY (HG)

707
MARINE BLUE (MB)



General Features

- All lockers arrive ready-to-use. Lockers ship fully-assembled and include one combination padlock per door for true out-of-the box use.
- Sloping top reduces dust accumulation and prevents item storage on locker tops.
- Closed metal bases provide a more finished appearance and eliminates the need to clean beneath lockers.
- Padlock Strike Plates are included for six tier doors.
- Order 3-wide units for best value. Order 1-wide units to complete quantity needed for each continuous row.



FEATURES:

- BODY CONSTRUCTION:** Knock-down, 24 gauge sheet steel
- BODY STYLES:** Single, double, triple and six tier
- DOOR:** 16 gauge, louvered for added ventilation, 18 gauge for box doors
- HINGES:** Continuous piano type
- HANDLE (wardrobe):** Stainless steel recessed handle with multi-point gravity lift-type latching. Recessed handle protects finish from being marred by padlock.
- HANDLE (box):** Box lockers include a projecting single-point friction catch door pull. No moving parts insures quiet maintenance-free operation.
- HOOKS:** One double prong ceiling hook and two single hooks per single and double tier opening. One double ceiling hook for triple tier. No hooks for six tier lockers
- COAT RODS:** Available for single tier at a nominal cost
- SHELVES:** Hat shelf is included in single tier lockers.
- LEGS:** 6" high legs are standard. Lockers without legs are available for a nominal charge



Locker Type	Overall Dimensions (In.)			Opening Dimensions (In.)			Item No. Parchment	Item No. Hallowell Gray	Item No. Marine Blue	Shpg Wt
	W	H	D	W	H	D				
SINGLE TIER WITH LEGS										
1 wide, 1 opening	12	78	12	9-1/4	69	11	2LYY5	2PFL4	2PFR7	59
3 wide, 3 openings	36	78	12	9-1/4	69	11	2LYY6	2PFL5	2PFR8	165
1 wide, 1 opening	12	78	15	9-1/4	69	14	2LYY7	2PFL6	2PFR9	63
3 wide, 3 openings	36	78	15	9-1/4	69	14	2LYY8	2PFL7	2PFT1	174
1 wide, 1 opening	12	78	18	9-1/4	69	17	2LYY9	2PFL8	2PFT2	66
3 wide, 3 openings	36	78	18	9-1/4	69	17	2LYZ1	2PFL9	2PFT3	180
DOUBLE TIER WITH LEGS										
1 wide, 2 openings	12	78	12	9-1/4	34	11	2LYZ2	2PFN1	2PFT4	69
3 wide, 6 openings	36	78	12	9-1/4	34	11	2LYZ3	2PFN3	2PFT5	191
1 wide, 2 openings	12	78	15	9-1/4	34	14	2LYZ4	2PFN5	2PFT6	73
3 wide, 6 openings	36	78	15	9-1/4	34	14	2LYZ5	2PFN7	2PFT7	201
1 wide, 2 openings	12	78	18	9-1/4	34	17	2LYZ6	2PFN9	2PFT8	79
3 wide, 6 openings	36	78	18	9-1/4	34	17	2LYZ7	2PFP2	2PFT9	219
TRIPLE TIER WITH LEGS										
1 wide, 3 openings	12	78	12	9-1/4	22-1/4	11	2LYZ8	2PFP4	2PFU1	84
3 wide, 9 openings	36	78	12	9-1/4	22-1/4	11	2LYZ9	2PFP5	2PFU2	230
1 wide, 3 openings	12	78	15	9-1/4	22-1/4	14	2LZA1	2PFP6	2PFU3	60
3 wide, 9 openings	36	78	15	9-1/4	22-1/4	14	2LZA2	2PFP7	2PFU4	180
1 wide, 3 openings	12	78	18	9-1/4	22-1/4	17	2LZA3	2PFP8	2PFU5	67
3 wide, 9 openings	36	78	18	9-1/4	22-1/4	17	2LZA4	2PFP9	2PFU6	186
SIX TIER WITH LEGS										
1 wide, 6 openings	12	78	18	9-1/4	10-1/2	11	2LZA5	2PFR1	2PFU7	70
3 wide, 18 openings	36	78	18	9-1/4	10-1/2	11	2LZA6	2PFR2	2PFU8	192
1 wide, 6 openings	12	78	15	9-1/4	10-1/2	14	2LZA7	2PFR3	2PFU9	73
3 wide, 18 openings	36	78	15	9-1/4	10-1/2	14	2LZA8	2PFR4	2PFV1	203
1 wide, 6 openings	12	78	18	9-1/4	10-1/2	17	2LZA9	2PFR5	2PFV2	78
3 wide, 18 openings	36	78	18	9-1/4	10-1/2	17	2PFL3	2PFR6	2PFV3	216

COLOR SELECTION

- 729 PARCHMENT (PT)
- 725 HALLOWELL GRAY (HG)
- 707 MARINE BLUE (MB)