

Stainless Steel Spring Retractable Reels

Air/Water/Oil - 3/8", 1/2", 3/4", 1" I.D.

Reelcraft's stainless steel hose reels are ideal for food processing, pre-rinse, wash down, chemical transfer and industrial-solvent handling. Also suitable for coastal, offshore and on-board ship in marine applications where the harsh environment of salt water spray requires the use of stainless steel hose reels. Swivels include Viton® O-rings.

Note: Standard latch parts are made from aluminium. Series 80000 and D80000 stainless reels have an aluminum fluid path. Stainless latch parts and fluid path are available as a standard option by placing a -S at the end. Example: OLS-S.



Series 7000



Series D9000

FEATURES

- ✓ Full-flow stainless steel shaft and swivel assures maximum product delivery.
Exception: Series 80000 - only on OLS-S models.
- ✓ Heavy duty brackets eliminate bending due to angular hose pull.
- ✓ Banded drive spring gives smooth automatic hose retrieval.
- ✓ Multi-position guide arm permits wall, floor, ceiling, pit or truck mounting.
- ✓ Nylon guide rollers reduce hose drag and abrasion.
- ✓ Pos-i-latch will maintain the desired working length of hose. Mechanism assures a positive latch of the hose.
- ✓ Series 7000 offers weatherproof gasketed spring motor, assures maximum service life.
- ✓ Vibration-proof self-locking fasteners assures assembly integrity.
- ✓ 304L grade of stainless steel.

Model without hose & bumper	Shipping Weight		Hose I.D.		Hose O.D.		Hose Length		Pressure		(F)NPTF Outlet	(F)NPTF Inlet	Size Index Page	Size Index #
	lbs	kg	in	mm	in	mm	ft	m	psi	bar	in	in		
Low and Medium Pressure Reels Maximum Temperature 210 °F (99 °C)														
5600 OLS	22	10	3/8	10	.600	15	35	11	500	35	3/8	3/8	9	2
5600 OMS	24	11	3/8	10	.710	18	30	9	3000	207	3/8	3/8	9	2
LC607 OLS*	35	16	3/8	10	.600	15	70	21	300	21	1/4	1/4	refer to reelcraft.com	
LC800 OLS*	33	15	1/2	13	.750	19	50	15	300	21	1/2	1/2	refer to reelcraft.com	
7800 OLS	41	19	1/2	13	.750	19	50	15	500	35	1/2	1/2	10	----
7600 OMS55	42	19	3/8	10	.710	18	66	20	3000	207	3/8	3/8	10	----
7800 OMS	43	20	1/2	13	.850	22	50	15	3000	207	1/2	1/2	10	----
82000 OLS	81	37	1/2	13	.750	19	100	30	500	35	1/2	1/2	13	1
82000 OMS	83	38	1/2	13	.850	22	75	23	1500	104	1/2	1/2	13	1
83000 OLS	81	37	3/4	19	1.188	30	50	15	500	35	3/4	3/4	13	1
83000 OMS	83	38	3/4	19	1.188	30	50	15	1250	86	3/4	3/4	13	1
D83000 OLS	84	38	3/4	19	1.188	30	75	23	500	35	3/4	3/4	13	2
D84000 OLS	92	42	1	25	1.375	35	50	15	500	35	1	1	13	3
D9200 OLS	115	52	1/2	13	.750	19	100	30	500	35	1/2	1/2	15	1
D9300 OLS	116	53	3/4	19	1.188	30	75	23	500	35	3/4	3/4	15	1
D9400 OLS	117	53	1	25	1.375	35	50	15	500	35	1	1	15	1
D9200 OMS	118	54	1/2	13	.850	22	75	23	3000	207	1/2	1/2	15	1
D9300 OMS	118	54	3/4	19	1.188	30	50	15	3000	207	3/4	3/4	15	1

For all metric thread connections over 1/2" add the suffix number 70 to indicate BSPT threads - example D83000 OLS70. Reference page 4 for guide arm positions. *Maximum temperature 150 °F (65 °C).

Model without Hose	Shipping Weight		Pressure		(F)NPTF Outlet	(F)NPTF Inlet	I.D.	1/4		6		3/8		10		1/2		13		3/4		19		1		25		Size Index # (see pg. 24)	
	lbs	kg	psi	bar	in	in		O.D.	.530	13	.710	18	.850	22	1.188	30	1.375	35											
Manual Crank Medium Pressure Reels Maximum Temperature 210 °F (99 °C)																													
HS18000 M	36	16	3000	207	1/2	1/2	Hose Length	425	130	300	91	200	61	---	---	---	---	---	---	---	---	---	---	---	---	---	---	1	
HS28000 M	35	16	3000	207	1/2	1/2		625	191	450	137	300	91	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	2
HS19000 M	38	17	3000	207	3/4	3/4		425	130	300	91	200	61	75	23	---	---	---	---	---	---	---	---	---	---	---	---	---	1
HS29000 M	36	16	3000	207	3/4	3/4		625	191	450	137	300	91	125	38	---	---	---	---	---	---	---	---	---	---	---	---	---	2
HS37000 L	47	21	500	35	1 (M)	1		---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	refer to reelcraft.com

Available Options

Mounting Brackets
See page 47

Inlet Hose Assemblies
See page 49

Replacement Bumpers
See page 49

Replacement Hoses
See page 50

Models listed with an icon can ship same day upon request when the order is received by 11:30 AM Eastern Time for quantities of 5 or fewer.

Indiana Warehouse Indiana & California Warehouses California Warehouse Canadian Warehouse

Customer Service: 1.855.634.9109
All Other Calls: 1.800.444.3134

