



<b>TOLERANCES</b> UNLESS OTHERWISE SPECIFIED 0.0 ±0.8 0.00 ±0.50 0.000 ±0.250 ANGLES ±1.0° ALL HOLE DIA. ±0.10 REMOVE ALL BURRS AND SHARP EDGES (CRITICAL DIMENSION) UNLESS SPECIFIED OTHERWISE - ALL DIM'S ARE IN MM - ALL INSIDE BEND RADII ARE 1-1.5 X MATERIAL THICKNESS	MATERIAL: CRS 1008, ???MM THK.	FINISH: SEE ARTICLE TEXT				ISO 1101/ANSI Y14.5 DATE NAME DRAWN CHECK	REFERENCE: PART NO: 3110000 ARTICLE NO:
	00 INITIAL RELEASE REV CHANGE DATE BY ECN CHK	RITTAL Corp. 1 Rittal Place Urbana, Ohio 43078		DRAWING NUMBER N/A		SCALE: 1.000 FORMAT: C SHEET: 1 OF 1	

THIS NOTE: ALL MATERIALS IN THIS PRODUCT MUST NOT CONTAIN LEAD, MERCURY, CADMIUM, HEXAVALENT CHROMIUM, POLYBROMINATED BIPHENYLS (PBB), AND POLYBROMINATED DIPHENYL ETHERS (PBDE), IN EXCESS OF THE LIMITS SPECIFIED IN THE RITTAL ROHS COMPLIANCE SPECIFICATION.