

# CUSTOMER SPECIFICATION DRAWING

PART NUMBER	DESCRIPTION	WIDTH & (THICKNESS) UNCOATED	CUT LENGTH [FEET]	WEIGHT [LBS.]
GRC204-P100	BAND, 200-300SS, COATED RED	.500 (.030)	50	2.89
GRC204-P200	BAND, 200-300SS, COATED ORANGE	.500 (.030)	50	2.89
GRC204-P300	BAND, 200-300SS, COATED YELLOW	.500 (.030)	50	2.89
GRC204-P400	BAND, 200-300SS, COATED GREEN	.500 (.030)	50	2.89
GRC204-P500	BAND, 200-300SS, COATED BLUE	.500 (.030)	50	2.89
GRC204-P900	BAND, 200-300SS, COATED BLACK	.500 (.030)	50	2.89
GRC206-P900	BAND, 200-300SS, COATED BLACK	.750 (.030)	50	4.14

**NOTES:**

- MATERIAL PER BAND-IT SPECIFICATIONS.

ABOVE SPECIFICATION CERTIFIED BY: \_\_\_\_\_ DATE: \_\_\_\_\_

TITLE: \_\_\_\_\_

UNLESS OTHERWISE NOTED:  
DIMENSIONS ARE IN INCHES  
AFTER FINISH

TOLERANCES:  
.X ..... ±0.100  
.XX ..... ±0.020  
.XXX ..... ±0.005  
.XXXX ..... ±0.001  
ANGLES ..... ±0.5°



A unit of ~~DEK~~ Corporation  
P.O. Box 16307  
Denver, Colorado U.S.A.

**PROPRIETARY AND CONFIDENTIAL**

THIS DRAWING WITH ALL  
CONTENTS IS PROPERTY OF  
BAND-IT. REPRODUCTION,  
DISCLOSURE OR MFG.  
OF MATTER SHOWN IS PROHIBITED  
WITHOUT WRITTEN PERMISSION.

DO NOT SCALE DRAWING

TITLE:

**ROLL BAND, COATED,  
GRAINGER**

DWG. NO.

**GRC202C**

REV -

SHEET 2 OF 2