














	XTRA™ CARTS: 4091 UTILITY CART		XTRA™ CARTS: 4096 UTILITY CART		XTRA™ CARTS: 4092 UTILITY CART		XTRA™ CARTS: 4093 UTILITY CART		XTRA™ EQUIPMENT CART: 4095 UTILITY CART		XTRA™ INSTRUMENT CART: 4094 UTILITY CART		EXECUTIVE SERVICE CART		CONVERTIBLE CART	
																
	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS
	300 LBS.	40.6" (L) X 20.0" (W) X 37.8" (H)	300 LBS.	40.6" (L) X 20.0" (W) X 51.0" (H)	300 LBS.	40.6" (L) X 20.0" (W) X 37.8" (H)	300 LBS.	40.6" (L) X 20.0" (W) X 37.8" (H)	300 LBS.	40.6" (L) X 20.75" (W) X 37.8" (H)	300 LBS.	40.6" (L) X 20.0" (W) X 37.8" (H)	300 LBS.	39" (L) X 21" (W) X 38" (H)	400 LBS.	45.2" (L) X 23.8" (W) X 34.4" (H)
AVAILABLE COLORS	BLACK, GRAY, OFF-WHITE		BLACK		OFF-WHITE		BLACK, OFF-WHITE		BLACK		GRAY		BLACK, PLATINUM		BLACK, RED	
HANDLE STYLE	ANGLED, ERGO. CURVED		ANGLED, ERGO. CURVED		ANGLED, ERGO. CURVED		ANGLED, ERGO. CURVED		ANGLED, ERGO. CURVED		ANGLED, ERGO. CURVED		FLAT, ERGO. CURVED		FLAT, ERGO. CURVED	
MATERIAL	STRUCTURAL WEB POLYPROPYLENE METAL UPRIGHTS		STRUCTURAL WEB POLYPROPYLENE METAL UPRIGHTS		STRUCTURAL WEB POLYPROPYLENE METAL UPRIGHTS		STRUCTURAL WEB POLYPROPYLENE METAL UPRIGHTS		STRUCTURAL WEB POLYPROPYLENE METAL UPRIGHTS		STRUCTURAL WEB POLYPROPYLENE METAL UPRIGHTS		STRUCTURAL WEB POLYPROPYLENE		HIGH-PRESSURE POLYPROPYLENE	
STORAGE CONFIGURATION	-		-		-		-		LOCKABLE DOORS		LOCKABLE DOORS SLIDING DRAWER		-		-	
CASTER OPTIONS	TPR QUIET, NON-MARKING		TPR QUIET, NON-MARKING		TPR QUIET, NON-MARKING		TPR QUIET, NON-MARKING		TPR QUIET, NON-MARKING		TPR QUIET, NON-MARKING		TPR QUIET, NON-MARKING		TPR (2 FIXED, 2 SWIVEL) QUIET, NON-MARKING	
CASTER SIZE	4"		4"		4"		4"		4"		4"		4"		5"	
LOCKING CASTERS																
ENCLOSED SIDE PANELS (2)					•				•							
ENCLOSED BACK PANEL							•		•							
ACCESSORIES																
REFUSE BIN (8 GAL.)	•		•		•		•		•		•		•		•	
UTILITY BIN (4 GAL.)	•		•		•		•		•		•		•		•	
UTILITY SLIDING DRAWER	•		•		•		•		•		•		•		•	

	SERVICE CARTS: 9T65-71 UTILITY CART		SERVICE CARTS: 3421 UTILITY CART		SERVICE CARTS: 3424-88 UTILITY CART		SERVICE CARTS: 3355-88 UTILITY CART		SERVICE CARTS: 3457 UTILITY CART	
										
	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS
	100 LBS.	31.5" (L) X 16.3" (W) X 36" (H)	150 LBS.	33.6" (L) X 18.6" (W) X 36.6" (H)	200 LBS.	33.6" (L) X 18.6" (W) X 37.8" (H)	300 LBS.	31" (L) X 18" (W) X 37.5" (H)	200 LBS.	33.6" (L) X 18.6" (W) X 37.8" (H)
AVAILABLE COLORS	BEIGE		BLACK, PLATINUM		BLACK, PLATINUM, OFF-WHITE, RED, GREEN, BLUE		PLATINUM		BLACK	
HANDLE STYLE	UPRIGHT		ANGLED, ERGO. CURVED		ANGLED, ERGO. CURVED		ANGLED, ERGO. CURVED		ANGLED, ERGO. CURVED	
MATERIAL	STRUCTURAL WEB POLYPROPYLENE METAL UPRIGHTS		STRUCTURAL WEB POLYPROPYLENE		STRUCTURAL WEB POLYPROPYLENE METAL UPRIGHTS		STRUCTURAL WEB POLYPROPYLENE		STRUCTURAL WEB POLYPROPYLENE	
STORAGE CONFIGURATION	-		-		-		-		LOCKABLE DOORS SLIDING DRAWER	
CASTER OPTIONS	TPR QUIET, NON-MARKING		TPR QUIET, NON-MARKING		TPR QUIET, NON-MARKING		TPR QUIET, NON-MARKING		TPR QUIET, NON-MARKING	
CASTER SIZE	3"		3"		4"		4"		4"	
LOCKING CASTERS										
ENCLOSED SIDE PANELS (2)	•		•						•	
ACCESSORIES										
ENCLOSED BACK PANEL										
REFUSE BIN (8 GAL.)			•		•		•		•	
UTILITY BIN (4 GAL.)			•		•		•		•	

		CASTERS
CASTER TREAD MATERIAL		TPR (THERMOPLASTIC RUBBER)
CASTER SIZE		4"
CASTER TYPE (QTY.)		2 SWIVEL; 2 FIXED
FLOOR SURFACES	EXCELLENT	ASPHALT, BRICK, CARPET, CONCRETE, LINOLEUM/TILE, TERRAZZO, AND WOOD
	GOOD	STEEL (RIBBED AND SMOOTH)
	FAIR	-
OPERATING CONDITIONS	EXCELLENT	METAL SCRAPS (SMALL OR LARGE)
	GOOD	WATER, STEAM, OR ANIMAL FATS
	FAIR	MILD OR HARSH CHEMICALS, OIL & GREASE
REPLACEMENT ITEM #		FG3424L60000 4" SWIVEL CASTER KIT
ADDITIONAL INFORMATION		TPR CASTERS ABSORB SHOCK AND PROVIDE FLOOR SURFACE PROTECTION AND QUIET OPERATION. CHEMICAL AND WATER RESISTANT.

SERVICE CARTS SELECTION GUIDE

To see our complete range of material handling solutions visit our online catalog at rubbermaidcommercial.com

RCP-385
#141734
©2015 Rubbermaid Commercial Products LLC
8900 Northpointe Executive Drive, Huntersville, NC 28078

