



SAFETY VIEW™ PLUS

KD Box Lockers



ADA 1 wide
4 openings

Six Tier,
3 wide,
18 openings



Sixteen person shown
with optional closed
base



4 Wide wall mount

BOX LOCKER FEATURES:

- BODY CONSTRUCTION:** Knock-down, 24 gauge,
- BODY STYLES:** Six tiers, Sixteen Person and wall mount
- DOOR:** High strength injection molded clear polycarbonate doors for content viewing
- HINGES:** Continuous piano type
- HANDLE:** Single-point projecting friction catch door pull prepared for both padlock or built-in lock.
- HOOKS:** None
- COAT RODS:** Standard on Sixteen person
- SHELVES:** None
- LEGS:** 6" high legs are standard. Lockers without legs are available for a nominal charge
- NOTES:** Meets UL flammability standards, Polycarbonate is approved by the Consumer Product Safety Commission (CPSC16CFR 1201)

GENERAL FEATURES:

- Number plates (#1-up) with mounting hardware are included
- Locks are not included.
- Safety-View plus doors provide an unobstructed view of locker contents
- Can be ordered fully-assembled or knock-down for assembly at destination.
- Order 3-wide units for best value. Order 1-wide units to complete quantity needed for each continuous row.

Locker Type	Overall Dimensions (In.)			Opening Dimensions (In.)			Knock-down Item No. Parchment	Fully-Assembled Item No. Parchment	Shpg Wt
	W	H	D	W	H	D			
SIX TIER WITH LEGS									
1 wide, 6 openings	12	78	12	9-1/4	10-1/2	11	4VEZ2	4HU15	64
3 wide, 18 openings	36	78	12	9-1/4	10-1/2	11	4VEZ3	4HU16	182
1 wide, 6 openings	12	78	15	9-1/4	10-1/2	14	4VEZ4	4HU17	67
3 wide, 18 openings	36	78	15	9-1/4	10-1/2	14	4VEZ5	4HU18	190
1 wide, 6 openings	12	78	18	9-1/4	10-1/2	17	4VEZ6	4HU19	70
3 wide, 18 openings	36	78	18	9-1/4	10-1/2	17	4VEZ7	4HU20	198
SIXTEEN PERSON									
16 openings	72	78	18	9-1/4	10-1/2	17		4HU21	180
4-WIDE WALL MOUNT									
4 openings	48	14-3/4	18	9-1/4	10-1/2	17		4HU22	50
ADA LOCKERS									
4 openings	12	78	12	9-1/4	10-1/2, 34	11	4VEZ8	4VFC4	64
4 openings	36	78	12	9-1/4	10-1/2, 34	11	4VEZ9	4VFC5	182
4 openings	12	78	15	9-1/4	10-1/2, 34	14	4VFA1	4VFC6	67
4 openings	36	78	15	9-1/4	10-1/2, 34	14	4VFA2	4VFC7	190
4 openings	12	78	18	9-1/4	10-1/2, 34	17	4VFA3	4VFC8	70
4 openings	36	78	18	9-1/4	10-1/2, 34	17	4VFA4	4VFC9	198

