

Knucklehead® Rechargeable Worklight

Specific lighting needs require specific tools. With the right lighting tool, you can identify potential or existing problems before they interrupt your ability to get the job done. In addition the costs savings of using the right tool over time will benefit your bottom line.

LEDs don't require periodic bulb replacement like incandescents and are virtually indestructible. Streamlight's revolutionary C4 technology combined with an innovative Streamlight-engineered reflector provides sharp, focused light that rivals incandescent intensity without giving up the durability and longevity of an LED. Since LEDs have a long life and won't burn out or won't break, they never need to be replaced. Your light will always be ready when you need it. More powerful and more economical, Streamlight rechargeable LED lighting tools pack a lot more power with ultra-bright white beams and long illumination times. They are extremely dependable and cost-efficient.

A "hands-free" working situation is much more productive, not to mention safer. No need to juggle while you work to complete a task with one hand while holding your flashlight in the other. Hands-free lighting tools are used wherever there's a need to use both hands (i.e. automotive, utility, electrical, firefighting, confined space or maintenance activities, among other situations). The Knucklehead features a removeable magnet and stowable hook to ensure a safer, "hands-free," more productive workplace by allowing the user to attach it to a metal surface (such as the hood of a car, or hang it to use as a drop light) It can also stand on its own or be laid on its side; and with a 210 degree articulating head that rotates 360 degrees you can direct the light where you need it.

The Knucklehead is a super versatile C4 LED flashlight. It features 2 LEDs that won't break or burn out so you'll never have to change a bulb. And you'll always have the power you need since it runs on either the rechargeable NiCd battery pack or 4 "AA" alkaline batteries.

Case Material: Housing, base and battery housing made from high impact super tough nylon offering exceptional durability. All openings are O-ring sealed for weather resistance. Circular rare-earth magnet surrounded by durable nickel plated steel housing. One way valve for case venting. Available in high visibility yellow or black.

Dimensions: Height: 9.20 in. (23.4 cm) Width: 2.85 in. (7.2 cm) Thickness (at magnet): 2.75 in. (7.0 cm)

Weight: NiCd: 23.1 oz (655 grams)* Alkaline: 18.3 oz (519 grams)*

Lens: Unbreakable polycarbonate with silicone anti-scratch coating assembled in a heavy duty bezel. O-ring sealed.

Light Source: Two (2) C4® LEDs, impervious to shock with a 50,000 hour lifetime.

Light Output: See chart. Dual wide pattern parabolic reflectors inset into larger textured reflector provide a smooth flood pattern for close-up work. Optimized electronics provide regulated intensity.

On/Off: Sonic welded push button switch designed for extremely long life. Rubber dome push button actuator provides easy operation even when wearing heavy gloves.

Run Time: See Chart. All claims to 10% of initial lumen output. Flash: 8 hrs continuous; Moonlight: 20 days continuous.

Battery: Industrial rechargeable nickel-cadmium 4.8 volt, 1.8 amp hour, 4 cell sub-C can be recharged up to 1,000 times. Optional four (4) "AA" alkaline non-rechargeable battery pack provides fast replacement with readily available batteries.

Charging: AC and DC one-hour fast chargers with full charge indicators designed specifically for AC or DC power sources. The universal Steady Charger, which requires up to 10 hours for a complete charge, can be used with 110V, 120V, 230V, 240V, or 12V DC by exchanging its charge cord. PiggyBack charger allows for simultaneously charging of the Knucklehead and a spare battery so you always have a light when you need it.

Features: Dual C4 LED technology for extreme brightness. 2 meter impact resistance tested.
Full 360 degree rotation head with 210 degrees of articulation. Removable magnet with 135 lb pull strength and integrated hook.
IPX4 rated for water resistant operation. All openings o-ring sealed. Serialized for positive identification.

Approvals: **NFPA**® Charger meets requirements of NFPA 1901-14.1.11.2 (2003) mounted in any position.

CE Meets applicable European Community Directives.

UL **USC** Class I, Division 2, Groups A,B,C,D; Class II, Division 2, Groups F,G; Class III, Temp Code: T4

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.



FL1 STANDARD	HIGH	LOW
	200 LUMENS	63 LUMENS
	3h 30min	16h
	68m	37m
	1150cd	350cd

Flash runs 8 hours
Moonlight mode runs 20 days

Part #	Description	UPC
<i>Without Charger</i>		
90601	Knucklehead - Black	080926-90601-3
90621	Knucklehead - Yellow	080926-90621-1
<i>Alkaline Model</i>		
90641	Knucklehead Alkaline Model - Black	080926-90641-9
90642	Knucklehead Alkaline Model - Yellow	080926-90642-6

Assembled in USA





Head rotates 360°
Articulates 210°



Powerful magnet is removeable.
Includes a cover to protect
painted surfaces



Integrated
stowable hook



Part #	Description	UPC
<i>Steady Charge with AC/DC charger holders</i>		
90607	Knucklehead 120V AC/ DC - Black	080926-90607-5
90627	Knucklehead 120V AC & DC - Yellow	080926-90627-3
90608	Knucklehead 230V AC & DC - Black	080926-90608-2
90628	Knucklehead 230V AC & DC - Yellow	080926-90628-0
90609	Knucklehead 240V AC & DC - Black	080926-90609-9
90629	Knucklehead 240V AC & DC - Yellow	080926-90629-7
90610	Knucklehead 100V AC & DC - Black	080926-90610-5
90630	Knucklehead 100V AC & DC - Yellow	080926-90630-3
90602	Knucklehead 120V AC - Black	080926-90602-0
90622	Knucklehead 120V AC - Yellow	080926-90622-8
90603	Knucklehead 230V AC - Black	080926-90603-7
90623	Knucklehead 230V AC - Yellow	080926-90263-5
90604	Knucklehead 240V AC - Black	080926-90604-4
90624	Knucklehead 240V AC - Yellow	080926-90264-2
90605	Knucklehead 100V AC - Black	080926-90605-1
90625	Knucklehead 100V AC - Yellow	080926-90625-9
90606	Knucklehead 12V DC - Black	080926-90606-8
90626	Knucklehead 12V DC - Yellow	080926-90626-6
<i>Steady Charge PiggyBack</i>		
90613	Knucklehead 120V AC/DC PiggyBack - Black	080926-90613-6
90633	Knucklehead 120V AC/DC PiggyBack - Yellow	080926-90633-4
90634	Knucklehead 230V AC/DC PiggyBack - Yellow	080926-90634-1
90614	Knucklehead 230V AC/DC PiggyBack - Black	080926-90614-3
90615	Knucklehead 240V AC/DC PiggyBack - Black	080926-90615-0
90635	Knucklehead 240V AC/DC PiggyBack - Yellow	080926-90635-8
90616	Knucklehead 100V AC/DC PiggyBack - Black	080926-90616-7
90636	Knucklehead 100V AC/DC PiggyBack - Yellow	080926-90636-5
<i>Fast Charge</i>		
90611	Knucklehead 120V AC FC - Black	080926-90611-2
90631	Knucklehead 120V AC FC - Yellow	080926-90631-0
90612	Knucklehead 230V AV FC - Black	080926-90612-9
90632	Knucklehead 230V AC FC - Yellow	080926-90632-7
90620	Knucklehead 12V DC FC - Black	080926-90620-4
90640	Knucklehead 12V DC FC - Yellow	080926-90640-2
<i>Fast Charge PiggyBack</i>		
90618	Knucklehead 120V AC FC PiggyBack - Black	080926-90618-1
90638	Knucklehead 120V AC FC PiggyBack - Yellow	080926-90638-9



Part #	Item	UPC
22050	DC2 direct wire charge cord (All Rechargeables)	080926-22050-8
22051	DC1 Charge Cord (All Rechargeables)	080926-22051-5
22311	120V AC charge cord	080926-22311-0
22241	240V AC charge cord	080926-22241-0
22664	230V AC charge cord	080926-22664-7
2266	100V AC charge cord	080926-22666-1
90010	Steady Charge (SC) Plug-In Charger Holder**	080926-90010-3
90011	AC Fast Charger (Includes Holder)	080926-90011-0
90012	DC #1 Fast Charger (Includes Holder)	080926-90012-7
90013	DC #2 Fast Charger (Includes Holder)	080926-90013-4
90110	Steady Charge (SC) PiggyBack® Charger	080926-90110-0
90111	AC PiggyBack® Fast Charger	080926-90111-7
90112	DC #1 PiggyBack® Fast Charger	080926-90112-4
90113	DC #2 PiggyBack® Fast Charger	080926-90113-1
90130	Div 1 Battery Pack (Blue Sleeve, NiCd Battery)	080926-90130-8
90338	Div 2 Battery Pack (Black Sleeve, NiCd Battery)	080926-90338-8
90400	Bank Charger (SC) 120V AC	080926-90400-2
90401	Bank Charger 12V DC	080926-90401-9
90542	Alkaline battery pack (Batteries not included)	080926-90542-9

**Cords not included



STREAMLIGHT



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax
www.streamlight.com ©Streamlight Knucklehead Flood Model 8/13