

















Stylus® Alkaline Battery-Powered Pen Light

FL 1 STANDARD	WHITE LED
	11 LUMENS
	24h
	24m
	140cd

FL 1 STANDARD	BLUE LED
	2 LUMENS
	24h
	21m
	110cd



FL 1 STANDARD	GREEN LED
	7 LUMENS
	24h
	15m
	59 cd

FL 1 STANDARD	RED LED
	2 LUMENS
	24h
	15m
	53 cd

Case Material: machined aluminum case with anodized finish and non-slip, knurled grip. Available in black, gold or silver, red, blue, US Flag

Dimensions/Weight: Length: 6.21"; 15.17 cm Diameter: 0.375"; 0.95 cm 1.1 oz; 31.19 grams*

Light Source: High intensity 5mm LED, impervious to shock with a 100,000 hour lifetime
Available in White, Blue (470nm), Red (624nm), Green (527nm), UV (365nm) or IR (880nm)

On/Off: Features a momentary blink switch and constant "on"

Battery: 3 "AAAA" size alkaline batteries.

Features: High intensity LED
Individually serialized for positive identification
IPX4/water-resistant. 2 meter impact resistance tested
Removable pocket clip.
Glare guard protector included in package
UL model available

Approvals**: UL Classified: Intrinsic Safety for Hazardous Locations; Class I, Div.1, Groups A,B,C,D, T3C "Classified" (applies to specific model)

C-UL UL Classified: Intrinsic Safety for Hazardous Locations; Class I, Div.1, Groups A,B,C,D, T3C; "Exia" (applies to specific model)

ATEX: II 1G EEx ia IIC T1; DEMKO 04 ATEX 0410949 (applies only to Black case/White or Blue LED combinations)

Most models meet applicable European Community Directives.



Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction

*With battery (included in purchase).

**See product for specific ratings.

Item		UPC	Part #
Stylus	Black with Red LED	080926-65006-0	65006
Stylus	Black with Blue LED	080926-65022-0	65022
Stylus	Black with Green LED	080926-65020-6	65020
Stylus	Black with White LED	080926-65018-3	65018
Stylus UL Listed	Black with White LED	080926-65058-9	65058
Stylus	Black with UV LED	080926-65069-5	65069
Stylus	OD with IR LED	080926-65186-9	65186
Stylus	US Flag with White LED	080926-65080-0	65080
<i>See reverse for additional part numbers</i>			





Item	UPC	Part #
Lanyard with Push Button Slide <i>(not shown)</i>	080926-72024-4	72024
AAAA Batteries – 6 pack	080926-65030-5	65030