Product leaflet

ProductModel No.Ordering No.Powered Air-Purifying Respirator (PAPR)SR 500H06-0121

Product Description

The SR 500 system is a belt mounted Powered Air-Purifying Respirator (PAPR) with tight fitting face pieces, loose fitting respirators or loose fitting hoods that protects against particulates, gases and vapors, or a combination. It is designed to be used in oxygen sufficient and non-immediately dangerous to life and health (IDLH) environments. The SR 500 PAPR system functions as an alternative to Air Purifying Respirators (APR) in all situations for which these are recommended. This applies particularly to work that is hard, warm or of long-duration. The filtered air is supplied through a breathing hose to the tight fitting face piece, loose fitting respirators or loose fitting hoods. The above-atmospheric pressure then generated prevents pollutants from the surroundings from penetrating into the breathing zone.

The characteristics of the SR 500 are as follows:


The battery is of lithium-ion type 3.6 Ah • Charging time around 2 hours • Equipped with two filters/combined filters • Operating time of up to 13 hours • The same control is used for starting, stopping and selection of operating status • Display with symbols • Equipped with automatic air flow control • Can be used together with a hood, face shield, full face mask.

Technical specification

	SR 500	42 CFR part 84 Full facepiece	42 CFR part 84 Loose-fitting facepiece
Air flow, min/max	6.2 CFM (175 I/min)/8.0 CFM (225 I/min)	4.1 CFM (115 I/min)	6.0 CFM (170 I/min)
Battery	14.8 V, 3.6 Ah	-	-
Operating times at 6.2 CFM / 8.0 CFM	и:		
P100 filter	13 h/8 h	≥ 4 h	≥ 4 h
Weight with P100 filter	≈ 53 Ounce (1.490 g)	-	-
Service temperature	14 to 131 °F (-10 to +55 °C), < 90 % RH	-	-
Storage temperature	4 to 104 °F (-20 to +40 °C), $<$ 90 % RH	-	-
Low flow warning level	6.2 CFM (175 I/min)	-	-
Protection factors¹: SR 540	25	-	-
Protection factors ² : SR 520, SR 530, SR 580/SR 584	SR 580, 1000	-	-
Protection factors¹: SR 200	1000	-	-
Approvals	NIOSH 42 CFR part 84	-	-

¹⁾ Specified by OSHA and applies generally to all full facepieces and loose-fitting facepieces together with Powered Air-Purifying Respirator (PAPR) when the employer implements a continuing, effective respirator program as required by this section (29 CFR 1910.134)


²⁾ APF (Assigned Protection Factor) documented in third party studies, according to OSHA 29 CFR 1910.134 and 3352-02-2009.



20 North Blossom St. East Providence, RI 02914

Office: 1-401-434-7300 Toll Free: 1-877-SUNDSTROM Fax: 1-401-434-8300

info@srsafety.com www.srsafety.com



Head-tops, spare parts and accessories				
Item				
No.	Part	Ordering No.		
1.	Hood SR 520 M/L	H06-0221		
1.	Hood SR 520 S/M	H06-0321		
2.	Hood SR 530	H06-0421		
3.	Face shield SR 540	H06-0521		
4.	Full face mask SR 200, PC visor	H01-1221		
4.	Full face mask SR 200, glass visor	H01-1321		
5.	PU hose SR 550 for SR 200	T01-1216		
5.	Rubber hose SR 551 for SR 200	T01-1218		
6.	Helmet with visor SR 580	H06-0812		
7.	Welding shield/Helmet with visor			
•	SR 584/SR 580	H06-8310		
8.	Battery HD SR 502, 3,6 Ah	T06-0101		
9.	Battery charger SR 513	R06-0103		
10.	Belt SR 508	R06-0101		
10. 11.	Rubber belt Leather belt	T06-0104 T06-0103		
12.	Harness SR 552	T06-0103		
13.	Flow meter SR 356	R03-0346		
14.	Charging station without chargers SR 506	T06-0108		
14.	Charging station, complete SR 516	T06-0111		
15.	PAPR SR 500, bare	R06-0121		
16.	Splash cover SR 514	T06-0114		
17.	Storage bag SR 505 w two compartments	T06-0102		
18.	Pre-filter holder SR 512	R06-0106		
19.	Particulate filter P100/HE, SR 510	H02-1321		
20.	Filter adapter SR 511	R06-0105		
21.	Pre-filter holder SR 5153 for SR 710	R01-0604		
22.	Particulate filter HE, SR 710	H02-1521		
23.	Chemical cartridge SR 532 OV/SD/CL/HC/H	HF H02-7121		
24.	Chemical cartridge SR 533			
	CL/HC/SD/FM/AM/MA	H02-7221		
25.	Gasket for PAPR	R06-0107		
26.	Hose SR 541 for SR 540	R06-0501		
27.	O-ring for breathing hose	R06-0202		
28.	Flat gasket for hose SR 541	R06-0506		
29.	Plug kit	R06-0703		

