



Duct Cover Shield

Surface Shields Tape



DESCRIPTION

Provides temporary closures on open duct-work. Prevents construction dust and debris from entering the duct work system, significantly reducing wipe down time and cost. The self-adhering protective film with a very high adhesion for all types of duct-work. The adhesive will not leave a residue on the metal after removal.

MAIN QUALITIES

- Self-adhering film
- High adhesion
- No residue upon removal
- Highly resistant to tears and punctures

APPLICATIONS

- Seal end of open metal ductwork
- During transport, storage & construction

TECHNICAL DATA

Color Blue
 Backing High strength LLDPE
 Adhesive Acrylic
 Thickness 2.0 mils
 Tensile Strength 4,084 psi
 Elongation 589%
 Dart Impact Resistance 100 grams

	Duct Cover Shield	Competition	Test Method
Tensile Strength (MD)	4084 psi	3800 psi	ASTM D882
Tensile Strength (CD)	2666 psi	3000 psi	ASTM D882
Elongation (MD)	589%	470%	ASTM D882
Elongation (CD)	761%	950%	ASTM D882
Dart Impact Test	100 grams	N/A	ASTM D1709
Adhesion	12.7 oz./in.	10.3 oz./in.	

Machine Direction (MD)

Cross Direction (CD)

Resists Tears & Punctures

High Adhesion

STANDARD SIZES

DCR224200B 24in x 200ft

DCR236200B 36in x 200ft

Surface Shields, Inc.
 www.surface Shields.com
1-800-913-5667

