

Multi Surface Protection Film

PRODUCT SPECIFICATION

DESCRIPTION

A moderate tack masking tape for use in interior applications. The product consists of a low density polyethylene backing, coated with a custom formulated water based acrylic adhesive.

PRODUCT APPLICATION

Remove over wrap from the product and locate the start of the film. Pull film off the roll slightly to determine the direction the film unwinds. Place film sticky side down on surface, secure start of the roll by applying slight pressure and then push roll in the desired direction. Apply slight pressure over the top of the film as you roll out to the desired length and then cut with a utility knife or sharp edge. To remove, simply lift film up at an edge and pull off. **Cannot be used on jobsite finished hardwood floors.**

PRODUCT STORAGE GUIDELINES

For best performance, store at room temperature and out of direct sunlight exposure. If Multi Surface Protection Film is stored in extreme conditions (over 95°F or below 40°F) allow product to return to room temperature prior to use.

NOMINAL VALUES

CONSTRUCTION

| | |
|-----------------|--|
| Backing | low density polyethylene - clear, blue, green, white |
| Adhesive | water based acrylic |
| Total Thickness | 3.0 nominal |

| PROPERTIES | US | METRIC | TEST METHOD |
|---------------------------|-------------|--------|-------------|
| Tensile | MD 3800 psi | ---- | ASTM D882 |
| | TD 3000 psi | ---- | ASTM D882 |
| Elongation | MD 470 | ---- | ASTM D882 |
| | TD 650 | ---- | ASTM D882 |
| Adhesion to steel (oz/in) | 8.0-12.0 | ---- | PSTC-1 |

LIMITED WARRANTY

Before using, the purchaser and/or user must determine suitability of this product for the intended use and the purchaser and/or user assumes all risks and liabilities in connection therewith. The sole obligation of the manufacturer, distributor, and/or seller of this product shall be replacement of the Multi Surface Protection Film product if notified of the defect within six months of the date of purchase. Such quantity of the product deemed defective shall be replaced or the amount of the purchase refunded and there shall be no liability to injury, loss or damages, either direct or consequential, arising out of the use or inability to use this product. The company disclaims all oral warranties of any kind. This limited warranty offered in connection with the manufacture and sale of the product is exclusive and in lieu of any warranties expressed, implied, or statutory, including without limitation and direct or implied warranty of merchantability or fitness for a particular use. **In the event of a claim, failure to notify manufacturer of incident prior to any remedy or replacement, voids any liability on the part of the manufacturer.**



800-913-5667
www.surface Shields.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.