



**Material Number:** 15E658

**Product Number:** WE10H138

**Part Description:** Shaft Coupler Hub,WE10,Bore Dia 1-3/8 In

**Product Type:** Dura-Flex BTS Hubs

**Coupling Size:** WE10

Properties and Performance
Bore size (in): 1-3/8
Bore Tolerance (in): +.0005 to +.0015
Setscrew Size: 3/8-16 UNC-2B
Setscrew Length (in): 3/4
Setscrew Torque Requirement (ft-lbs): 23
Keyseat: 5/16 x 5/32
Material Type: Low Carbon Steel
MAX RPM (rpm): 7500
Component Weight (lbs.): 3.6

TB Wood's reserves the right to change above reference information as necessary.