



Material Number: 15E660

Product Number: WE10H178

Part Description: Shaft Coupler Hub,WE10,Bore Dia 1-7/8 In

Product Type: Dura-Flex BTS Hubs

Coupling Size: WE10

Properties and Performance
Bore size (in): 1-7/8
Bore Tolerance (in): +.0005 to +.0015
Setscrew Size: 3/8-16 UNC-2B
Setscrew Length (in): 1/2
Setscrew Torque Requirement (ft-lbs): 23
Keyseat: 1/2 X 1/4
Material Type: Low Carbon Steel
MAX RPM (rpm): 7500
Component Weight (lbs.): 3

TB Wood's reserves the right to change above reference information as necessary.