



Material Number: 15E637

Product Number: WE2H78

Part Description: Shaft Coupling Hub,WE2,Bore Dia. 7/8 In.

Product Type: Dura-Flex BTS Hubs

Coupling Size: WE2

Properties and Performance
Bore size (in): 7/8
Bore Tolerance (in): +.0005 to +.0015
Setscrew Size: 1/4-20 UNC-2B
Setscrew Length (in): 3/8
Setscrew Torque Requirement (ft-lbs): 7
Keyseat: 3/16 x 7/8
Material Type: Low Carbon Steel
MAX RPM (rpm): 7500
Component Weight (lbs.): .40

TB Wood's reserves the right to change above reference information as necessary.