



Material Number: 15E646

Product Number: WE4H118

Part Description: Shaft Coupling Hub,WE4,Bore Dia 1-1/8 In

Product Type: Dura-Flex BTS Hubs

Coupling Size: WE4

| Properties and Performance |
|--|
| Bore size (in): 1-1/8 |
| Bore Tolerance (in): +.0005 to +.0015 |
| Setscrew Size: 5/16-18 UNC-2B |
| Setscrew Length (in): 1/2 |
| Setscrew Torque Requirement (ft-lbs): 14 |
| Keyseat: 1/4 x 1/8 |
| Material Type: Low Carbon Steel |
| MAX RPM (rpm): 7500 |
| Component Weight (lbs.): 1.30 |

TB Wood's reserves the right to change above reference information as necessary.