



Material Number: 15E649

Product Number: WE4H158

Part Description: Shaft Coupling Hub,WE4,Bore Dia 1-5/8 In

Product Type: Dura-Flex BTS Hubs

Coupling Size: WE4

Properties and Performance
Bore size (in): 1-5/8
Bore Tolerance (in): +.0005 to +.0015
Setscrew Size: 5/16-18 UNC-2B
Setscrew Length (in): 1/4
Setscrew Torque Requirement (ft-lbs): 14
Keyseat: 3/8 x 3/16
Material Type: Low Carbon Steel
MAX RPM (rpm): 7500
Component Weight (lbs.): 0.9

TB Wood's reserves the right to change above reference information as necessary.