



Material Number: 15E645

Product Number: WE4H78

Part Description: Shaft Coupling Hub,WE4,Bore Dia 7/8 In

Product Type: Dura-Flex BTS Hubs

Coupling Size: WE4

Properties and Performance
Bore size (in): 7/8
Bore Tolerance (in): +.0005 to +.0015
Setscrew Size: 5/16-18 UNC-2B
Setscrew Length (in): 3/4
Setscrew Torque Requirement (ft-lbs): 14
Keyseat: 3/16 x 7/8
Material Type: Low Carbon Steel
MAX RPM (rpm): 7500
Component Weight (lbs.): 1.50

TB Wood's reserves the right to change above reference information as necessary.