



Description: **STANDARD PVC**

PRODUCT SPECIFICATIONS

SAVE-T PVC STRIP & SHEET

Roll Size		
THICKNESS:	.040" to .250"	
WIDTH:	4" to 60"	
Material Description		
FINISH:	Double Polished	
COLOR:	Clear	
Physical Properties		
Property	Result	ASTM
Hardness (15 sec. delay)	79 A Scale	D2240
Tensile Strength:	2400 PSI	D412
Ultimate Elongation:	350%	D412
Graves Tear:	440	D1004
100% Modulus:	1400 PSI	D412
Stiffness: (-20°F)	44,000 PSI	-
Brittleness Temp:	-33° F	D746
Operating Temp:	0° F to 150° F	-
Specific Gravity:	1.21	D792
Density:	75 lbs. cu.ft.	C-177
Thermal Conductivity (K):	.73	C-177
Thermal Resistance (R):	1.37	C-177
Water Absorption:		
UV Resistance:	YES	
Flammability Rating:	Select Material Compliant with CA State Fire Marshal	
Shipped in a box on 6" cores		

Note: The information contained herein is believed to be reliable but no representations, guarantees or warranties of any kind are made as to its accuracy or suitability for particular applications.

TMI, LLC
5350 Campbells Run Road
Pittsburgh, PA 15205-9738
Web-Site: www.tmivinylsolutions.com

Toll Free: 800-888-9750
Phone: 412-787-9750
Fax: 412-787-3665
E-mail: vinylsolutions@tmi-pvc.com