

## The Bookcase that Means Business

Tennsco's newest Welded Bookcase offers a unique 18" depth and 35<sup>7</sup>/<sub>8</sub>" width that allows a wide range of materials to be stored safely. Now you can place all types of materials especially those that have a large footprint. If your application involves large legal format folders, expandable envelopes or any other larger media, you'll be pleased that Tennsco's bookcases help your materials remain safe from overhanging folders.

## 18" Deep Welded Bookcases

### Deeper Shelf Storage

18" Deep Welded Bookcase offers a deeper cabinet for larger materials such as oversized ledgers and legal documents.

### Reinforced for Durability

Extra strength is added in the welding process, providing years of heavy use.

### Shelf Capacity

Durable shelves are designed tough. Each shelf is capable of supporting 150 lbs.

### Locking Tabs

Locking tabs on the sides and back are spaced evenly apart and allow for easy installation, creating binder-sized openings.

### Easy Adjustability

Each shelf adjusts vertically in 2<sup>5</sup>/<sub>64</sub>" increments to accommodate materials of any size. Shelves can also be adjusted on 12<sup>1</sup>/<sub>2</sub>" centers which are clearly identified... perfect for binders.

### Integrated Shelf Support Tabs

Built-in shelf support tabs mean no clips to lose.

### Raised Base

Keeps materials safe from mops and damaging cleaners.



Above unit is shown in our Champagne Putty finish.

### Maximum Rigidity

Shelves have multiple bends at front and rear for additional strength.

### Smooth, Clean Lines

Exposed bolts are completely eliminated for a clean professional appearance. Unit tops have no overhang, so side-to-side units will fit flush together.

## Mobile Casters



All 18" deep bookcases can be retrofitted with mobile casters. Ideal for offices that need to share information yet keep contents safe and accessible.