

# Z-Line Components

## Post Options

### Post Options

Match posts with your needs: Use SUR posts for your most demanding applications. Use EUR for light or medium weight applications and in conjunction with ZTP posts. Use ZTP as an intermediate common "T" post.



**SUR**  
Heavy Upright Post



**EUR**  
Standard Upright Post



**ZTP**  
Intermediate Upright Post

## Shelf Options



### Particle Board Decking

Industrial grade  $\frac{5}{8}$ " particle board decking provides a sturdy work surface that is both strong and economical.



### Wire Decking

Select wire decking for better visibility of items. Meets Factory Mutual fire codes.

## Support Options



### Low Profile Support Options

Maximizes shelf openings in light to medium duty support applications. Available in 14 or 11 gauge steel. Load capacities range from 600 to 800 lbs., depending upon steel gauge and shelf size.



### Medium Profile Support Options

Special V-beam design provides heavy-duty support at an economical price. Available in 16 or 14 gauge steel. Load capacities range from 600 to 1,000 lbs., depending upon steel gauge and shelf size.



### Wide Profile Shelf Supports

Heavy-duty  $2\frac{3}{4}$ " high beam to laterally support decking in longer spans. For load capacities ranging from 1,250 lbs. to 2,500 lbs., depending upon shelf size.



### Channel Beams

Extra heavy-duty  $3\frac{1}{4}$ " high beam for maximum strength. Supports spans 48" and longer. Load capacities range from 1,600 lbs. to 2,500 lbs., depending upon shelf size.



### Front to Back Shelf Deck Support

For added support for decking on long spans. Used with wide profile shelf supports and Channel Beams.



### Medium Profile Front to Back Shelf Supports

Added support on long spans of medium profile shelf supports. Snap-in design for easy installation.