

E100PB SERIES: 1 CHANNEL/120VAC/60Hz PRODUCT DETAILS & INFORMATION

SERIES E101PB (SPST) SERIES E103PB (DPST)		DRY CONTACT RATINGS		
LOAD TYPE	120VAC	240VAC	277VAC	
Resistive	30A	30A	12A	
Inductive	30A	30A	12A	
Ballast	20A	6A	6A	
Tungsten	5A	5A	5A	
Pilot Duty	470VA	470VA	690VA	
Motor	1HP	2HP		

all are 20A resistive @28VDC

SERIES E120PB (SPDT)					DRY CONTACT RATINGS	
LOAD TYPE	120VAC		240VAC		277VAC	
	NO	NC	NO	NC	NO	NC
Resistive	20A	10A	20A	10A	6A	3A
Inductive	20A	10A	20A	10A	6A	3A
Ballast	6A	3A	6A	3A	6A	3A
Tungsten	5A	3A	5A	3A		
Pilot Duty	470VA	275VA	470VA	275VA	690VA	
Motor	1HP	¼HP	2HP	½HP		

NO 20A resistive @ 28VDC, NC 20A resistive @ 28VDC