



# JUSTRITE® Product

# New!

# ESSENTIALS



## The best Type I Safety Can just got better!

### New!



### Stainless Steel Flame Arrester

- Precision arrester screen stops flashback ignition to reduce fire risks
- Superior chemical resistance
- Excellent corrosion protection
- Long length for safe insertion of gas nozzle
- Faster liquid flow

### New!



### Large ID Zone

- Identify contents to reduce misuse or incompatible mixtures
- Designate department location, work shift, crew or individual user



## Type I Safety Cans

Compliant and economical Justrite Type I safety cans reduce fire risks and make everyday use of flammables easier and safer. Protection features include a 3-1/2" (88mm) long chemical resistant stainless steel flame arrester that stops flashback ignition, provides faster liquid flow, and offers exceptional durability. The self-venting, self-closing leakproof lid prevents ruptures from pressure build-up and controls vapors and spills. Warning label includes an extra large ID zone for user labeling of contents to avoid misuse, reduce the potential for incompatible mixtures, or may be used to designate department or individual owner. Made of galvanized steel with a tough powder paint finish, can capacities 1 gallon (4L) and above have ample headspace to accommodate oil additives.

**100% leak tested. 10 year warranty.**  
**Meets OSHA and NFPA.**  
**FM approved, UL/ULC listed,**  
**Carb compliant, TÜV certified.**

Built-in safety with unsurpassed quality backed by an exclusive 10-year warranty



Fully compliant. Independently fire tested and approved.

Over →

## Type I Red Steel Safety Cans for Flammables

Model Number	Capacity Gallon (Liter)	Dimensions Outer Dia. x H (mm)	Approval/Listing Regulation	Ship Wt. Lbs/Kg
10001	1 Pt (0.5)	4 <sup>3</sup> / <sub>8</sub> " x 6 <sup>3</sup> / <sub>4</sub> " (117 x 172)	FM,UL/ULC,TÜV	2/1
10101	1 Qt (1)	4 <sup>3</sup> / <sub>8</sub> " x 8 <sup>1</sup> / <sub>4</sub> " (117 x 210)	FM,UL/ULC,TÜV	2/1
7110100	1 (4)	9 <sup>1</sup> / <sub>2</sub> " x 11" (241 x 279)	FM,UL/ULC,TÜV	4/2
7120100	2 (7.5)	9 <sup>1</sup> / <sub>2</sub> " x 13 <sup>3</sup> / <sub>4</sub> " (241 x 349)	FM,UL/ULC,TÜV	5/2
7125100	2 <sup>1</sup> / <sub>2</sub> (9.5)	11 <sup>3</sup> / <sub>4</sub> " x 11 <sup>1</sup> / <sub>2</sub> " (298 x 292)	FM,UL/ULC,TÜV	6/3
7150100	5 (19)	11 <sup>3</sup> / <sub>4</sub> " x 16 <sup>7</sup> / <sub>8</sub> " (298 x 429)	FM,UL/ULC,TÜV	8/4

Replaces Models  
Being Discontinued

Model Number
—
10301, 10201
10501
10555, 10701
10801



7110100  
1 gal. (4L)



7120100  
2 gal. (7.5L)



7125100  
2<sup>1</sup>/<sub>2</sub> gal. (9.5L)



7150100  
5 gal. (19L)

## Type I Yellow Steel Safety Cans for Diesel Fuel

Model Number	Capacity Gallon (Liter)	Dimensions Outer Dia. x H (mm)	Approval/Listing Regulation	Ship Wt. Lbs/Kg
10011	1 Pt (0.5)	4 <sup>3</sup> / <sub>8</sub> " x 6 <sup>3</sup> / <sub>4</sub> " (117 x 172)	FM,UL/ULC,TÜV	2/1
10111	1 Qt (1)	4 <sup>3</sup> / <sub>8</sub> " x 8 <sup>1</sup> / <sub>4</sub> " (117 x 210)	FM,UL/ULC,TÜV	2/1
7110200	1 (4)	9 <sup>1</sup> / <sub>2</sub> " x 11" (241 x 279)	FM,UL/ULC,TÜV	4/2
7120200	2 (7.5)	9 <sup>1</sup> / <sub>2</sub> " x 13 <sup>3</sup> / <sub>4</sub> " (241 x 349)	FM,UL/ULC,TÜV	5/2
7125200	2 <sup>1</sup> / <sub>2</sub> (9.5)	11 <sup>3</sup> / <sub>4</sub> " x 11 <sup>1</sup> / <sub>2</sub> " (298 x 292)	FM,UL/ULC,TÜV	6/3
7150200	5 (19)	11 <sup>3</sup> / <sub>4</sub> " x 16 <sup>7</sup> / <sub>8</sub> " (298 x 429)	FM,UL/ULC,TÜV	8/4

Replaces Models  
Being Discontinued

Model Number
—
10311, 10211
10511
10551, 10711
10811

## Type I Blue Steel Safety Cans for Kerosene

Model Number	Capacity Gallon (Liter)	Dimensions Outer Dia. x H (mm)	Approval/Listing Regulation	Ship Wt. Lbs/Kg
7110300	1 (4)	9 <sup>1</sup> / <sub>2</sub> " x 11" (241 x 279)	FM,UL/ULC,TÜV	4/2
7120300	2 (7.5)	9 <sup>1</sup> / <sub>2</sub> " x 13 <sup>3</sup> / <sub>4</sub> " (241 x 349)	FM,UL/ULC,TÜV	5/2
7125300	2 <sup>1</sup> / <sub>2</sub> (9.5)	11 <sup>3</sup> / <sub>4</sub> " x 11 <sup>1</sup> / <sub>2</sub> " (298 x 292)	FM,UL/ULC,TÜV	6/3
7150300	5 (19)	11 <sup>3</sup> / <sub>4</sub> " x 16 <sup>7</sup> / <sub>8</sub> " (298 x 429)	FM,UL/ULC,TÜV	8/4

Replaces Models  
Being Discontinued

Model Number
—
10310, 10210
10510
10710
10810

## Type I Green Steel Safety Cans for Oils

Model Number	Capacity Gallon (Liter)	Dimensions Outer Dia. x H (mm)	Approval/Listing Regulation	Ship Wt. Lbs/Kg
7110400	1 (4)	9 <sup>1</sup> / <sub>2</sub> " x 11" (241 x 279)	FM,UL/ULC,TÜV	4/2
7120400	2 (7.5)	9 <sup>1</sup> / <sub>2</sub> " x 13 <sup>3</sup> / <sub>4</sub> " (241 x 349)	FM,UL/ULC,TÜV	5/2
7125400	2 <sup>1</sup> / <sub>2</sub> (9.5)	11 <sup>3</sup> / <sub>4</sub> " x 11 <sup>1</sup> / <sub>2</sub> " (298 x 292)	FM,UL/ULC,TÜV	6/3
7150400	5 (19)	11 <sup>3</sup> / <sub>4</sub> " x 16 <sup>7</sup> / <sub>8</sub> " (298 x 429)	FM,UL/ULC,TÜV	8/4

Replaces Models  
Being Discontinued

Model Number
—
10312
10712
10812

## Poly Funnel for Type I Steel Safety Cans

Model Number	Description	Dimensions Outer Dia x L (mm)	Approval/Listing Regulation	Ship Wt. Ctn Lbs/Kg
11202Y	Poly Funnel fits Type I Steel cans	1/2" x 11 1/4" (13 x 286)	—	1/1

Color Coding  
Reduces Accidents

# Cans with Funnels Value Packages

## Type I Red Steel Safety Cans with Funnels Value Packages

Model Number	Capacity Gallon (Liter)	Dimensions Outer Dia. x H (mm)	Approval/Listing Regulation	Ship Wt. Lbs/Kg
7110110	1 (4)	9 <sup>1</sup> / <sub>2</sub> " x 11" (241 x 279)	*FM,UL/ULC,TÜV	4/2
7120110	2 (7.5)	9 <sup>1</sup> / <sub>2</sub> " x 13 <sup>3</sup> / <sub>4</sub> " (241 x 349)	*FM,UL/ULC,TÜV	5/2
7125110	2 <sup>1</sup> / <sub>2</sub> (9.5)	11 <sup>3</sup> / <sub>4</sub> " x 11 <sup>1</sup> / <sub>2</sub> " (298 x 292)	*FM,UL/ULC,TÜV	6/3
7150110	5 (19)	11 <sup>3</sup> / <sub>4</sub> " x 16 <sup>7</sup> / <sub>8</sub> " (298 x 429)	*FM,UL/ULC,TÜV	8/4

Replaces Models  
Being Discontinued

Model No
—
10502
10552, 10702
10802, 50802



## Type I Yellow Steel Safety Cans with Funnels Value Packages

Model Number	Capacity Gallon (Liter)	Dimensions Outer Dia. x H (mm)	Approval/Listing Regulation	Ship Wt. Lbs/Kg
7110210	1 (4)	9 <sup>1</sup> / <sub>2</sub> " x 11" (241 x 279)	*FM,UL/ULC,TÜV	4/2
7120210	2 (7.5)	9 <sup>1</sup> / <sub>2</sub> " x 13 <sup>3</sup> / <sub>4</sub> " (241 x 349)	*FM,UL/ULC,TÜV	5/2
7125210	2 <sup>1</sup> / <sub>2</sub> (9.5)	11 <sup>3</sup> / <sub>4</sub> " x 11 <sup>1</sup> / <sub>2</sub> " (298 x 292)	*FM,UL/ULC,TÜV	6/3
7150210	5 (19)	11 <sup>3</sup> / <sub>4</sub> " x 16 <sup>7</sup> / <sub>8</sub> " (298 x 429)	*FM,UL/ULC,TÜV	8/4

7150110



Funnel Aids in Pouring

To aid pouring into smaller openings, hinged Poly Funnel attaches easily to all sizes of Type I steel cans. Design allows you to fill the can without removing the funnel and takes up less space when storing. Durable, large polypropylene rounded bowl provides protection from splashing and spillage.

## Type I Blue Steel Safety Cans with Funnels Value Packages

Model Number	Capacity Gallon (Liter)	Dimensions Outer Dia. x H (mm)	Approval/Listing Regulation	Ship Wt. Lbs/Kg
7110310	1 (4)	9 <sup>1</sup> / <sub>2</sub> " x 11" (241 x 279)	*FM,UL/ULC,TÜV	4/2
7120310	2 (7.5)	9 <sup>1</sup> / <sub>2</sub> " x 13 <sup>3</sup> / <sub>4</sub> " (241 x 349)	*FM,UL/ULC,TÜV	5/2
7125310	2 <sup>1</sup> / <sub>2</sub> (9.5)	11 <sup>3</sup> / <sub>4</sub> " x 11 <sup>1</sup> / <sub>2</sub> " (298 x 292)	*FM,UL/ULC,TÜV	6/3
7150310	5 (19)	11 <sup>3</sup> / <sub>4</sub> " x 16 <sup>7</sup> / <sub>8</sub> " (298 x 429)	*FM,UL/ULC,TÜV	8/4

## Type I Green Steel Safety Cans with Funnels Value Packages

Model Number	Capacity Gallon (Liter)	Dimensions Outer Dia. x H (mm)	Approval/Listing Regulation	Ship Wt. Lbs/Kg
7110410	1 (4)	9 <sup>1</sup> / <sub>2</sub> " x 11" (241 x 279)	*FM,UL/ULC,TÜV	4/2
7120410	2 (7.5)	9 <sup>1</sup> / <sub>2</sub> " x 13 <sup>3</sup> / <sub>4</sub> " (241 x 349)	*FM,UL/ULC,TÜV	5/2
7125410	2 <sup>1</sup> / <sub>2</sub> (9.5)	11 <sup>3</sup> / <sub>4</sub> " x 11 <sup>1</sup> / <sub>2</sub> " (298 x 292)	*FM,UL/ULC,TÜV	6/3
7150410	5 (19)	11 <sup>3</sup> / <sub>4</sub> " x 16 <sup>7</sup> / <sub>8</sub> " (298 x 429)	*FM,UL/ULC,TÜV	8/4

7125110



Approval/ Listing and Regulation Key

FM – FM Global tested and approved  
UL/ULC – Underwriters Laboratories listed in the U.S. and Canada  
TÜV – Technical Inspection Association certified

\*Approvals apply to safety can