



**JUSTRITE®** **Product**

**New!**

# ESSENTIALS



## AccuFlow™

**Fast, precision pouring makes it the easiest-to-use**

**Type II Safety Can ... bar none!**

**New!**

**AccuFlow™ Innovative Manifold**

- Fastest, smoothest, most controlled pouring
- Quick-open fill port with ergonomic lift lever for easy filling
- Auto venting protects against pressure build-up



**New!**

**Stainless Steel Flame Arrester**

- Precision arrester screen stops flashback ignition to reduce fire risks
- Superior chemical resistance
- Excellent corrosion protection
- Long length for safe insertion of gas nozzle
- Faster liquid flow



**New!**

**Large ID Zone**

- Identify contents to reduce misuse or incompatible mixtures
- Designate department location, work shift, crew or individual user



### The Inside Secret!



**Engineered for the highest performance in safety, compliance, and convenience.**

Over →



Phone: 800-798-9250  
Fax: 800-488-5877  
www.justritemfg.com



7250130

7225130

7220120

7210120



Going beyond protection and compliance, AccuFlow™ Type II Safety Cans provide fast, precision pouring when handling flammable liquids. Patented, innovative manifold automatically vents for smooth, slug-free liquid flow, while the comfortable Safe-Squeeze® trigger offers maximum control when pouring. A 9" (229mm) flexible metal hose ensures offers targeted pouring into small openings. Fill port with ergonomically designed handle makes filling easier than ever.

Protection features include a long lasting, stainless steel flame arrester that dissipates heat to prevent flashback ignition and a gasketed, self-closing leak tight lid that automatically vents to guard against rupture or explosion. Warning label with extra large ID zone permits user to identify contents, department location, or individual user name. All can sizes have extra capacity for mixing in additives for two cycle engines.

**100% leak tested. 10 year warranty.**  
**Meets OSHA and NFPA.**  
**FM approved, UL/ULC listed,**  
**Carb compliant, TÜV certified.**

### Type II Red Accuflow™ Safety Cans for Flammables

Model Number	Capacity Gallon (Liter)	Hose Dia. Size(mm)	Can Dimensions Outer Dia. x H (mm)	Approval/Listing Regulation	Ship Wt. Lbs/Kg	Replaces Models Being Discontinued	
						UNO™ Number	Type II Number
7210120	1 (4)	5/8"(16)	9½" x 10½" (241 x 267)	FM,UL/ULC,TÜV	7/3	10368	10327, 10345
7220120	2 (7.5)	5/8"(16)	9½" x 13¼" (241 x 337)	FM,UL/ULC,TÜV	8/4	10468,10568	10527
7225120	2½ (9.5)	5/8"(16)	11¾" x 12" (298 x 305)	FM,UL/ULC,TÜV	8/4	10668,10768	10728
7225130	2½ (9.5)	1"(25)	11¾" x 12" (298 x 305)	FM,UL/ULC,TÜV	8/4	10667,10767	10721
7250120	5 (19)	5/8"(16)	11¾" x 17½" (298 x 445)	FM,UL/ULC,TÜV	10/5	10868	10828
7250130	5 (19)	1"(25)	11¾" x 17½" (298 x 445)	FM,UL/ULC,TÜV	10/5	10867	10821

### Type II Yellow Accuflow™ Safety Cans for Diesel Fuel

Model Number	Capacity Gallon (Liter)	Hose Dia. Size(mm)	Can Dimensions Outer Dia. x H (mm)	Approval/Listing Regulation	Ship Wt. Lbs/Kg	Replaces Models Being Discontinued	
						UNO™ Number	Type II Number
7210220	1 (4)	5/8"(16)	9½" x 10½" (241 x 267)	FM,UL/ULC,TÜV	7/3	10368Y	10326
7220220	2 (7.5)	5/8"(16)	9½" x 13¼" (241 x 337)	FM,UL/ULC,TÜV	8/4	10468Y,10568Y	10526
7225220	2½ (9.5)	5/8"(16)	11¾" x 12" (298 x 305)	FM,UL/ULC,TÜV	8/4	10668Y,10768Y	10729
7225230	2½ (9.5)	1"(25)	11¾" x 12" (298 x 305)	FM,UL/ULC,TÜV	8/4	10667Y,10767Y	10732
7250220	5 (19)	5/8"(16)	11¾" x 17½" (298 x 445)	FM,UL/ULC,TÜV	10/5	10868Y	10829
7250230	5 (19)	1"(25)	11¾" x 17½" (298 x 445)	FM,UL/ULC,TÜV	10/5	10867Y	10832

### Type II Blue Accuflow™ Safety Cans for Kerosene Fuel

Model Number	Capacity Gallon (Liter)	Hose Dia. Size(mm)	Can Dimensions Outer Dia. x H (mm)	Approval/Listing Regulation	Ship Wt. Lbs/Kg	Replaces Models Being Discontinued	
						UNO™ Number	Type II Number
7210320	1 (4)	5/8"(16)	9½" x 10½" (241 x 267)	FM,UL/ULC,TÜV	7/3	10368B	—
7220320	2 (7.5)	5/8"(16)	9½" x 13¼" (241 x 337)	FM,UL/ULC,TÜV	8/4	10468B,10568B	10527B
7225320	2½ (9.5)	5/8"(16)	11¾" x 12" (298 x 305)	FM,UL/ULC,TÜV	8/4	10668B,10768B	10728B
7225330	2½ (9.5)	1"(25)	11¾" x 12" (298 x 305)	FM,UL/ULC,TÜV	8/4	10667B,10767B	10720
7250320	5 (19)	5/8"(16)	11¾" x 17½" (298 x 445)	FM,UL/ULC,TÜV	10/5	10868B	10828B
7250330	5 (19)	1"(25)	11¾" x 17½" (298 x 445)	FM,UL/ULC,TÜV	10/5	10867B	10820

### Type II Green Accuflow™ Safety Cans for Oils

Model Number	Capacity Gallon (Liter)	Hose Dia. Size(mm)	Can Dimensions Outer Dia. x H (mm)	Approval/Listing Regulation	Ship Wt. Lbs/Kg	Replaces Models Being Discontinued	
						UNO™ Number	Type II Number
7210420	1 (4)	5/8"(16)	9½" x 10½" (241 x 267)	FM,UL/ULC,TÜV	7/3	10368E	—
7220420	2 (7.5)	5/8"(16)	9½" x 13¼" (241 x 337)	FM,UL/ULC,TÜV	8/4	10468E,10568E	10527E
7225420	2½ (9.5)	5/8"(16)	11¾" x 12" (298 x 305)	FM,UL/ULC,TÜV	8/4	10668E,10768E	10728E
7225430	2½ (9.5)	1"(25)	11¾" x 12" (298 x 305)	FM,UL/ULC,TÜV	8/4	10667E,10767E	10726
7250420	5 (19)	5/8"(16)	11¾" x 17½" (298 x 445)	FM,UL/ULC,TÜV	10/5	10868E	10828E
7250430	5 (19)	1"(25)	11¾" x 17½" (298 x 445)	FM,UL/ULC,TÜV	10/5	10867E	10826



Left to right: 7250220, 7210420, 7225320

**Color Helps Designate Contents and Segregate Liquids**

Type II AccuFlow™ safety cans are available in four colors that are suitable for the storage of liquids. Now it's easy to differentiate between various types of liquids and avoid costly errors when more than one type of liquid is needed at a worksite.

For added safety and convenience, the label on Justrite® safety cans includes an extra large ID Zone to make it easy for the user to mark can contents, designate department/shift/user, etc.

#### Approval/ Listing and Regulation Key

- FM – FM Global tested and approved
- UL/ULC – Underwriters Laboratories listed in the U.S. and Canada
- TÜV - Technical Inspection Association certified

