



Hydrometer Cases

VEE GEE®, w/ Cap & Internal Padding

Cat. No.	Description	Length (mm / in)	List Price (Each)
66CS-8	Case/PVC	216 / 8.5	26.50
66CS-8F	Case/PVC (Short)	165 / 6.5	27.50
66CS-13	Case/PVC	343 / 13.5	29.00
66CS-13J	Case/PVC (Wide Body)	343 / 13.5	29.00
66CS-16	Case/PVC	420 / 16.5	32.00

NOTE: All Hydrometer Cases are assortable for the 10+ quantity discount. Custom sizes available; please contact us for details.

Hydrometer Cases and Jars Selection Chart

Case	Internal Dimension
66CS-8	210mm max
66CS-8F	175mm (6604,672xH, 673xH & 165mm)
66CS-13	340mm max
66CS-13J	340mm max (67151H, 67152H, 6613-Series)
66CS-16	390mm max

Jar	Jar Capacity	Max. Hydrometer Length
21000-250	250mL	215mm max
21000-500	500mL	330mm max
21000-1000	1L	385mm max

Hydrometer Series	Description	Approx. Length (mm)	Uses Case	Uses (Jar)
6601-Series	Brix	330	66CS-13	500mL
6601T-Series	Brix w/Thermometer	370	66CS-16	1L
6601TS-Series	Brix w/SafetyBlue Thermometer	370	66CS-16	1L
6602, 6603-Series	Specific Gravity	305	66CS-13	500mL
6603DS-Series	Specific Gravity & Baume	305	66CS-13	500mL
6604-Series	Specific Gravity	165	66CS-8F	250mL
6605-1	Specific Gravity & Baume: Universal	380	66CS-16	1L
6608-Series	API	195	66CS-8	250mL
6609-Series	Baume: Heavy	305	66CS-13	500mL
6611-Series	CaCl ₂ or NaCl	305	66CS-13	500mL
6612-1	Alcohol: Tralle & Proof	305	66CS-13	500mL
6612-2TS	Alcohol: Tralle & Proof w SafetyBlue Thermometer	355	66CS-16	1L
6613-Series	Alcohol: Proof, IRS	230-305	66CS-13J	500mL
6614TS-Series	Plato w SafetyBlue Thermometer	360-380	66CS-16	1L
672xH, 673xH-Series	API:ASTM	165	66CS-8F	250mL
675xHTS-Series	API:ASTM w/SafetyBlue Thermometer	380	66CS-16	1L
6782H-67141H-Series	Specific Gravity: ASTM	360-330	66CS-13	500mL
67101HTS	LPG w/SafetyBlue Thermometer	365	66CS-16	500mL
6715xH	Specific Gravity or Soil Colloids: ASTM	280	66CS-13J	500mL

Hydrometer Certification, NIST, 3-Point

States Corrections To The Readings That Are Traceable to NIST

Cat. No.	Description	List Price (Each)
6600	NIST Certification, 3-Point Includes Case	289.00

NOTE: Hydrometer model must be specified at point of order. Certification pricing does not include the price of the hydrometer. Certification is nonrefundable and cannot be cancelled once ordered. Please allow extra time for delivery.



Hydrometer Jars

Made from Borosilicate Tubing

Cat. No.	Description	Pack Qty.	Case Qty.	List Price Pack	List Price Case
21000-250	250 mL Hydrometer Jar	2	12	15.40	84.00
21000-500	500 mL Hydrometer Jar	2	12	24.20	132.00
21000-1000	1000 mL Hydrometer Jar	1	6	20.90	114.00

Prices subject to change.

