

## WARN 1000AC

### Ideal for use anywhere 120-Volt AC power is available

Wherever there is a wall socket, you can now pull or drag just about anything anywhere with the versatile WARN 1000AC Utility Winch. The 1000AC winch delivers 1,000 lbs. of pulling capacity, 43' of wire rope, a long duty cycle and legendary WARN durability make this a tool you can rely on to get the job done.

#### 1000AC SPECS

**Part Number:** 80010 \* *Product not sold in Canada*

**Capacity:** 1,000 lbs (454 kg)

**Motor:** Permanent Magnet

**Horsepower:** 0.8hp (600w)

**Power Source:** 120V AC, GFCI

**Switch Type:** Remote With 10' (3 m) Lead

**Geartrain:** Planetary, Differential Planetary

**Gear Ratio:** 261:1

**Clutch (freespooling):** Pull & Turn

**Brake:** Self Braking Transmission

**Warranty:** 1 year limited

**Wire Rope:** 3/16" x 43' (4.8mm x 13.1 m)

**Length:** 15.42" (39.2cm)

**Drum Diameter:** 2.0" (52mm)

**Fairlead:** Hawse

**Hole Pattern:** 4 holes 3.1" x 2.5" (78.8mm x 63.5mm)

**Weight:** 26.5 lbs (12.0 kgs)

#### PERFORMANCE SPECS (first layer of drum)

Load Lbs. (kg)	Line Speed Ft./min. (M/min)	Motor Current, Amps (At 120 VAC)
0 (0)	9.8 (3.0)	0.4
250 (113)	7.9 (2.4)	1.8
500 (227)	6.9 (2.1)	3.1
750 (340)	6.1 (1.8)	4.5
1000 (454)	5.5 (1.7)	6