

WARN 2000 DC

A compact utility winch packed with full-sized features

Although this winch might be smaller in size, it's big on value. The WARN 2000 DC Utility Winch has all of the features you'll want, and its small size allows it to be mounted in tight spots. Designed to pull lighter loads, this winch will help you move more material in less time.

- 2,000 lb. (907 kg) capacity with plenty of power for smaller jobs
- 12-volt power for portability - ideal for use on trailers or hitch mounts
 - Outstanding duty cycle, durability, and features
- Strong 1.6 horsepower permanent magnet DC motor with outstanding duty cycle
 - 35' of 3/16" (10.7m of 4.7mm) wire rope with hook and clasp
- Remote plug accepts 12' (3.7m) corded remote (included) or optional wireless remote kit
 - Ergonomic, multi-directional clutch lever
 - Durable, differential planetary geartrain
- Dynamic braking for great control and holding power
 - Hawse fairlead

2000 DC SPECS

Part Number: PN 92000

Rated Line Pull: 2,000 lbs. (907 kgs)

Motor: Permanent Magnet

Switch Type: Remote Control

Brake: Self-locking gear train (Rated Load Holding)

Wire Rope: 3/16" X 35' (10.7 m)

HP: 1.6 HP 3.0"

Power: 12 volt DC

Gear Train: Split Ring Gear

Clutch: Knob, pull and turn

Drum Diameter: 1-1/4 in. (3.18 cm)

Fairlead: Hawse

Hole Pattern: 2 Holes on 3.1" (7.87 cm) center

Gear Ratio: 153:1

Electrical Leads: 2 - 6' (1.8 m)

Weight: 18 lbs. (8.2 kg.)

Warranty: 1 year limited

12V DC PERFORMANCE SPECS (first layer of drum)

Line Pull Lbs.(Kgs.)	Line Speed FT./min(M/min.)	Motor Current	Pull by layer layer/Lbs(Kgs.)
0	7.2(2.2)	6.7	1/2000(907)
500(226.8)	6.8(2.0)	24.1	2/ 1504 (683)
1000(453.6)	5.7(1.7)	44.7	3/1348(612)
1500(680.4)	4.8(1.4)	72.0	4/1222(555)
2000(907)	4.2(1.3)	80.0	5/1117(507)

Above performance specs are based on first layer of drum

