

## WARN 3000 ACI

With a 3,000 lbs. pulling capacity, a TEFC Induction AC motor for a long duty cycle and 100' of 5/16" wire rope, the 3000 ACI just what you need when you need a heavy-hauling AC powered winch. The perfect fixed-mount station winch.

### 3000 ACI SPECS

**Part Number:** PN 93000

**Capacity:** 3,000 lbs. (1361 kgs) single line

**Switch Type:** Drum switch/station type

**Motor:** TEFC induction AC motor

**HP:** 0.7 hp 56C

**Power:** 115/230 volt

**Geartrain:** 3-Stage planetary

**Clutch:** Lever-Actuated Sliding

**Brake:** Dynamic and Mechanical Braking

**Wire Rope:** 5/16" X 100' (30.5 m)

**Fairlead:** None

**Electrical Leads:** None

**Weight:** 76 lbs. (34.5kg)

**Warranty:** Limited One Year

**Replacement Wire Rope:** PN 27110

### 120V AC PERFORMANCE SPECS (first layer of drum)

| Line Pull<br>Lbs.(Kgs.) | Line Speed<br>FT./min(M/min.) | Motor Current<br>(At 120V AC) | Pull by Layer:<br>layer/lbs (kgs.) |
|-------------------------|-------------------------------|-------------------------------|------------------------------------|
| 0(0)                    | 12.2(3.7)                     | 9.1 Amps                      | 1/3000(1361)                       |
| 1000(453.6)             | 8.8(2.7)                      | 11.0 Amps                     | 2/2700(1225)                       |
| 1500(680.4)             | 8.8(2.7)                      | 12.7 Amps                     | 3/2460(1116)                       |
| 2000(907.2)             | 8.6(2.6)                      | 14.8 Amps                     | 4/2250(1021)                       |
| 2500(1134)              | 8.5(2.6)                      | 17.7 Amps                     | 5/2070(939)                        |
| 3000(1360.8)            | 8.1(2.5)                      | 20.9 Amps                     |                                    |