

# D6200-3 Series

★★★★  
**300 lbs.**  
LOAD CAPACITY  
Type IA  
Duty Rating



**THE SAME REACH AS A  
STANDARD EXTENSION LADDER  
IN A COMPACT DESIGN!**



Convenient to store and maneuver



Easy to transport on  
compact vehicles



Versatile - Use indoors or outdoors





# D6200-3 Series

- Innovative three section design reduces shorter than standard two section extension ladders
- Convenient to maneuver and carry around on job sites
- Easy to transport inside and on top of vehicles
- More overlapping rung locations for improved working comfort
- 1<sup>5</sup>/<sub>8</sub>" D-Rung design ALFLO® Rung to rail connection for Twist-Proof® performance



★★★★★  
**300** LOAD CAPACITY  
 lbs.  
 Combined weight of User and Materials  
 Type IA Duty Rating

## SPECIFICATIONS

Model No.	Ladder Size	Total Length of Sections	Max. Working Length	Approx. Shipping Wt. (lbs.)
<b>D6216-3</b>	16'	18'	13'	40.5
<b>D6220-3</b>	20'	23'	17'	54.0
<b>D6224-3</b>	24'	27'	21'	61.0
<b>D6228-3</b>	28'	31'	26'	74.5
<b>D6232-3</b>	32'	35'	29'	81.0

## STORAGE SIZE COMPARISON (Standard 2-piece vs. Compact 3-piece)

Ladder Size	D6200-2 2 Section	D6200-3 3 Section
<b>16'</b>	8' 3"	6' 4"
<b>20'</b>	10' 3"	8' 4"
<b>24'</b>	12' 3"	9' 4"
<b>28'</b>	14' 3"	11' 4"
<b>32'</b>	16' 3"	12' 4"



2 sets of durable, pivoting rung locks



Comfortable standing surface



Retainer strap secures ladder for storage & transport

D6224-3 Model Shown