

C324028S4 WIRE CONTAINER



PRODUCT SHEET

C324028S4 without Casters

C324028S4C with Casters

The side and base mesh is 2"x2" (5 x5 cm). The gate is a ½ Drop Front Gate with only four latch bolts to engage for quick and easy assembly. The **C324028S4** has four way entry for forklifts or pallet jacks, with a clearance of 4.5" (11.4 cm). Can be stacked up to four high fully loaded. Heavy-duty base design for long life cycles. The casters are 4"x2" Phenolic, 2 Rigid and 2 Swivel.

Weight (lbs/kg)	115/52 without casters 133/60 with casters	Capacity	4000/1814 without casters 2800/1270 with casters
Overall dimensions W x L x H (in/cm)	32 x 40 x 34½ 81 x 102 x 88	Inside dimensions W x L x H (in/cm)	30 x 38 x 28 76 x 96.5 x 71
Surface Treatment	Plating	Electro-Zinc	
Accessories	Casters, Security Lid, Vertical Divider, Bar Runners, Caster Brakes, Colors (special order)		
Shipment	Packed Folded & Stacked (with or without casters)		



NashvilleWire

P R O D U C T S

For more information about this product:

nwpsales@nashvillewire.com

www.nashvillewire.com

800-448-2125