

WOOSTER®

QUALITY FOR ALL



Everyone Deserves
HIGH-QUALITY
Paint Applicators.

After the paint dries, a consumer who chooses Wooster realizes that the right tools can achieve great results with less effort. As every retailer knows, a satisfied customer means repeat business. Wooster has an applicator program that includes favorites from the contractor market, as well as DIY brands that are made with the same attention to quality. The fast, smooth coverage provided by Wooster paintbrushes and rollers offers lasting value—and higher margins for the success of retailers everywhere.

SILVER TIP®

Semi-professional quality at a great value! Silver Tip is made with a blend of white and silver Wooster CT™ polyester that virtually eliminates brushmarks. Thin, soft, flexible ends provide exceptional leveling and smoothing. Perfect for latex paints, applying enamels to metal, or polyurethanes on wood. Birch hardwood handle for a professional touch.

- 5221 angle sash in 1½", 2", 2½" and 3" sizes
- 5225 short handle angle sash 2"
- 5224 thin angle sash 1½", 2" and 2½" sizes
- 5220 flat sash in 2", 2½" and 3" sizes
- 5222 varnish in 1½", 2", 2½" and 3" sizes
- 5223 wall in 3" size



GOLDEN GLO®

Best-quality Golden Glo brushes really shine. Longer, solid, gold nylon/sable polyester filaments provide high paint capacity for less dipping and less effort. (No cheap, hollow filaments in Golden Glo.) Exploded-Tip® processing creates thick, soft flags on the brush tips to deliver a smooth finish. Large handle provides more comfort. Fastest coverage with all paints—acrylic, latex, and oil-based.

- Q3118 wall/trim in 1", 1½", 2", 2½", 3" and 4" sizes
- Q4119 angle sash in 1½" and 2" sizes



SOFTIP®

No other brush paints smoother and faster at this price point! Wooster Softip features fine, feather-like filament ends that reduce brushmarks. The famous, short, pearl-yellow handle offers comfort and control as well as shelf appeal. Softip provides good results in all paints, latex and oil-based.

- Q3108 wall/trim in 1", 1½", 2", 2½", 3" and 4" sizes
- Q3208 angle sash in 1", 1½", 2" and 2½" sizes
- 5971 two pack contains 2" angle sash and 3" wall



SHORTCUT®

Make painting easier on the wall-to-ceiling line, window frames, and more! Wooster Shortcut brushes feature a soft, Shergrip® elastomeric handle designed to provide extra comfort and control. Full-size heads mean these small brushes still offer smooth, fast paint coverage! Synthetic blend for all paints and water-based stains.

- B3211 synthetic 2" angle sash, clip strips
- Q3211 synthetic 2" angle sash, display box
- Q3109 synthetic 3" wall/trim



YACHTSMAN®

More than 50 years since their launch, Yachtsman brushes are still a top-selling Wooster line on land and sea. Natural white China bristle is soft and resilient for the finest results with oil-based varnishes, enamels, paints, stains, and urethanes. Wood grain, solid black plastic handle resists moisture and solvents. Shorter sash handle for tight spaces.

Z1120 varnish/wall in 1", 1½", 2", 2½", 3" and 4" sizes
Z1121 angle sash in 1½", 2" and 2½" sizes



What's the advantage of a nylon/polyester blend like Golden Glo has?

While polyester gives a brush stiffness for control, nylon holds precise tipping for a smoother finish, resists wear, and cleans much better than polyester. Nylon/polyester blends are by far the most popular professional paintbrush choice.

AMBER FONG®

Experienced traditional painters will say for oil-based coatings there's nothing like the finish China bristle can provide. Amber Fong is the natural bristle equivalent of popular Wooster Softip brushes. Soft, amber-brown bristles deliver an extra-fine finish with all oil-based paints, enamels, varnishes, and stains. Short handle makes the brush easy to control.

1123 wall/trim in 1", 1½", 2", 2½", 3" and 4" sizes
1233 angle sash in 1½" and 2" sizes



SHORTCUT® WHITE BRISTLE

Grab easier painting by the handle! Wooster Shortcut paintbrushes have a soft Shergrip® handle for a comfortable painting experience with added control. Their full-size heads mean these brushes are never "Short" on coverage. White China bristle excels in all oil-based paints, stains, and varnishes. Take a Shortcut for cupboards, furniture, and more.

B3215 white bristle 2" angle sash, clip strips
Z3215 white bristle 2" angle sash, display box



SUPER DOO-Z®

A favorite of both professional and DIY painters, for price and performance! Super Doo-Z is the most imitated roller in the industry, but it's made only by Wooster. Interlocked fibers resist shedding for a "no lint" finish. Dense fabric reduces dripping and spatter. Perfect for use with all paints, enamels, and varnishes in sheens from flat to gloss.

- R206 with 3/16" nap in 4", 7" and 9" lengths
- R205 with 3/8" nap in 4", 7", 9", 14" and 18" lengths
- R204 with 1/2" nap in 4", 7" and 9" lengths
- R203 with 3/4" nap in 4", 9" and 18" lengths
- R905 Super Doo-Z 9" x 3/8" roller kit

GOLDEN FLO™

High-capacity Golden Flo rollers achieve fast "no skip" coverage with fewer trips to the paint tray. Good density fibers resist matting for a smoother finish. Now a low-shed knit, Golden Flo is best for all flat or eggshell paints, stains, and waterproofing.

- RR660 with 3/8" nap in 4", 9" and 18" lengths
- RR661 with 1/2" nap in 9" length
- RR662 with 3/4" nap in 9" length
- RR664 with 1 1/4" nap in 9" length
- R914 Golden Flo 9" x 3/8" roller kit

ROLLER 3-PACKS

More than one room, coat, or color? Super Doo-Z and Golden Flo, our top-selling consumer rollers, are available in 3-packs for added value. Both options create a nice finish on most walls and ceilings.

- R725 Super Doo-Z 3-pack with 3/8" nap in 9" length
- RR726 Golden Flo 3-pack with 3/8" nap in 9" length



Wooster DIY rollers have our consistently round, polypropylene core. It resists water, solvents, and cracking to add to the overall performance and life of the roller.

JUMBO-KOTER®

Miniroller systems can deliver BIG results! Extra-smooth rolling action means Jumbo-Koter frames take the work out of painting kitchens, baths, closets, and trim. Wooster Jumbo-Koter fabrics are the same as full-size rollers for invisible touchup or edging. Lock the frame onto a Sherlock GT® pole or use it with any threaded extension handle.

Jumbo-Koter Super Doo-Z® & Golden Flo™

Use these minirollers in conjunction with our full-size covers for seamless results. When a smooth finish is the goal, shed-resistant Super Doo-Z is perfect for all paints, flat to gloss. For no-skip coverage and fast results, use Golden Flo with all flat or eggshell paints and stains.

RR113 Super Doo-Z frame and cover 4½" x 3/8"

RR313 Super Doo-Z roller 2-pack 4½" x 3/8"

RR115 Golden Flo frame and cover 4½" x 3/8"

RR315 Golden Flo roller 2-pack 4½" x 3/8"



THE PRIMER™

Shed-resistant tan fabric provides a smooth base coat. Maximum hiding power with all latex and oil-based primers, including stain-killing, bonding, or vapor blocking. Use on drywall, plaster, smooth wood, and other medium-textured surfaces.

R201 with 3/8" nap in 9" length



501™ ROLLER FRAME

Reach for a painting experience that's more comfortable than average DIY frames. Made with a combination of Wooster Shergrip® and durable polypropylene, the 501's non-slip grip is perfect for hot or tired hands. Sturdy five-wire cage fully supports covers for smooth rolling. An extra ring of Shergrip material at the bottom of the grip helps to lock the frame onto threads for extension pole use.

R501 in 9" size



WOOSTER[®]

QUALITY FOR ALL

- **Faster, smoother finish with less effort**
- **Solid customer satisfaction and repeat business**
- **Higher quality products, higher margins for you**

SHOW & SELL

This 4-foot merchandiser is packed full of Wooster paint tools. The perfect mix for DIY painters, it includes brushes, rollers and kits, as well as sturdy frames and deluxe paint trays. Colorful and informative layout helps customers find the right applicator for the job. Wooster also offers 2-foot and 3-foot product assortments.

3988 4' brush and roller merchandiser



WOOSTER[®]

The Wooster Brush Company • Wooster, OH • Reno, NV • 800-392-7246 • www.woosterbrush.com

C-201202 7/12