



NOTES:

1. TUBE SIZE : 3/4 x 1/2 x 1/2
2. PIPE SIZE - PIPE FITTING : 3/4 x 3/4
3. PEX SIZE : 3/4
4. FITTING CONNECTION TYPE : PEX
5. TUBE FITTING MATERIAL : Polyalloy
6. MAX. PRESSURE : 80 psi
7. TEMP. RANGE : 33° to 200°F
8. STANDARDS : ASTM F877, ASTM F2159, CAN CSA B137.5 NSF 1 4 NSF 61

COMPONENT

Coupling

GRAINGER

100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE

2.06

10A562

Coupling, Polyalloy, PEX, 3/4" x 3/4" Pipe

UNIT

INCH

SHEET

1 of 1