



NOTES:

1. SERIES: RD
2. ITEM: Hydraulic Ram
3. BODY MATERIAL: Steel
4. OIL CAPACITY: 50.31 cu. in.
5. MAX. PRESSURE: 10,000 psi
6. NOMINAL CAPACITY: 25 tons
7. EFFECTIVE AREA: 4.91 sq. in.
8. MAX. PUSH CAPACITY: 25 tons
9. COLLAR THREAD SIZE: 2-3/4"-16
10. PLUNGER THREAD SIZE: 1-1/2"-12
11. CYLINDER TYPE: General Purpose
12. SINGLE ACTING/DOUBLE ACTING: Double Acting

COMPONENT	High Pressure Hydraulic Cylinders
------------------	-----------------------------------



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.48

18Y541
Univer Cylinder, 25 tons, 10-1/4inL Stroke

UNIT
INCH
SHEET
1 of 1